



DIMENSIONS SHOWN AS: inches (mm)

EXCHANGER SIZE	DIMENSIONS											
	A		B		C		D		N1		N2	
	inches	mm	inches	mm	inches	mm	inches	mm	inches	mm	inches	mm
WSX-62-2E3	36 3/8	924	23	584	15	381	27	686	1 1/2	38	1	25
WSX-63-2E3	48 3/8	1229	35	889	27	686	39	991	2	51	1	25
WSX-64-2E3	60 3/8	1534	47	1194	39	991	51	1295	2 1/2	64	1	25
WSX-65-2E3	72 3/8	1838	59	1499	51	1295	63	1600	2 1/2	64	1	25
WSX-66-2E3	84 3/8	2143	71	1803	63	1600	75	1905	3	76	1	25
WSX-67-2E3	96 3/8	2448	83	2108	75	1905	87	2210	3	76	1	25
WSX-68-2E3	108 3/8	2753	95	2413	87	2210	99	2515	3	76	1	25

NOZZLE SCHEDULE				
SERVICE	MARK	SHELL SIDE	MARK	TUBE SIDE
INLET	N1	AS PER TABLE	N5	2 (51) NPT
OUTLET	N2	AS PER TABLE	N6	2 (51) NPT
VENT	N4	3/4 (19) NPT		

NOTES:

1. SUPPORTS SUPPLIED ONLY IF SPECIFIED ON ORDER.
2. NOZZLE SIZES SHOWN ARE RECOMMENDED FOR MAXIMUM EXCHANGER LIFE.
3. FABRICATED TO ASME CODE SECTION VIII DIVISION 1 AND LATEST ADDENDA.
4. DRAWING IS NOT TO SCALE.
5. ALL DIMN'S $\pm 1/8$ (3) UNLESS OTHERWISE SHOWN.

DESIGN CONDITIONS				
	SHELL		TUBES	
DESIGN PRESSURE	150 PSIG	1034 KPa	150 PSIG	1034 KPa
DESIGN TEMPERATURE	375 °F	191 °C	375 °F	191 °C
MIN. DESIGN METAL TEMP.	35 °F	1.7 °C	35 °F	1.7 °C
HYDRO. TEST PRESSURE	225 PSIG	1551 KPa	300 PSIG	2068 KPa
CONTENTS	STEAM		WATER	

CUSTOMER: _____
 LOCATION: _____
 ENGINEER: _____
 ORDER No.: _____
 PROJECT/JOB: _____
 LOCATION: _____
 TAG: _____ (QUOTE # _____)

TITLE	G.A. 150 LB. WSX SERIES HEAT EXCHANGERS	A R M S T R O N G				NUMBER	WSX-6-2P-E3- (3)	REV.			
DATE:	12 / 01 / 94	BY:	D.C.R.	TEL :	(416) 755-2291	MONTREAL - CANADA	TEL : (514) 421-2424	BUFFALO - N. Y.	TEL: (716) 693-8813	COLCHESTER - U.K.	TEL: (44) 120-657-9491