



EXCHANGER SIZE * - BAFFLE SPACING	DIMENSIONS											
	A		B		C		D		N1		N2	
	inches	mm	inches	mm	inches	mm	inches	mm	inches	mm	inches	mm
WX-184-2*-2	68 3/8	1737	31 1/4	794	16 3/4	425	52	1321	8	203	8	203
WX-185-2*-2	80 3/8	2042	43 1/4	1099	28 3/4	730	64	1626	8	203	8	203
WX-186-2*-2	92 3/8	2346	55 1/4	1403	40 3/4	1035	76	1930	8	203	8	203
WX-187-2*-2	104 3/8	2651	67 1/4	1708	52 3/4	1340	88	2235	8	203	8	203
WX-188-2*-2	116 3/8	2956	79 1/4	2013	64 3/4	1645	100	2540	8	203	8	203
WX-189-2*-2	128 3/8	3261	91 1/4	2318	76 3/4	1949	112	2845	8	203	8	203
WX-1810-2*-2	140 3/8	3566	103 1/4	2623	88 3/4	2254	124	3150	8	203	8	203
WX-1811-2*-2	152 3/8	3870	115 1/4	2927	100 3/4	2559	136	3454	8	203	8	203
WX-1812-2*-2	164 3/8	4175	127 1/4	3232	112 3/4	2864	148	3759	8	203	8	203
WX-1813-2*-2	176 3/8	4480	139 1/4	3537	124 3/4	3169	160	4064	8	203	8	203
WX-1814-2*-2	188 3/8	4785	151 1/4	3842	136 3/4	3473	172	4369	8	203	8	203
WX-1815-2*-2	200 3/8	5090	163 1/4	4147	148 3/4	3778	184	4674	8	203	8	203

NOZZLE SCHEDULE				
SERVICE	MARK	SHELL SIDE	MARK	TUBE SIDE
INLET	N1	AS PER TABLE	N5	8 (203) FLG
OUTLET	N2	AS PER TABLE	N6	8 (203) FLG
DRAIN	N3	1/2 (13) NPT		
VENT	N4	3/4 (19) NPT		

NOTES: 1. SUPPORTS SUPPLIED ONLY IF SPECIFIED ON ORDER.  
 2. NOZZLE SIZES SHOWN ARE RECOMMENDED FOR MAXIMUM EXCHANGER LIFE.  
 3. FABRICATED TO ASME CODE SECTION VIII DIVISION 1 AND LATEST ADDENDA.  
 4. DRAWING IS NOT TO SCALE.  
 5. ALL DIMN'S ±1/8 (3) UNLESS OTHERWISE SHOWN.

DESIGN CONDITIONS				
	SHELL		TUBES	
DESIGN PRESSURE	150 PSIG	1034 KP <sub>0</sub>	150 PSIG	1034 KP <sub>0</sub>
DESIGN TEMPERATURE	375 °F	191 °C	375 °F	191 °C
MIN. DESIGN METAL TEMP.	40 °F	4.4 °C	40 °F	4.4 °C
HYDRO. TEST PRESSURE	225 PSIG	1551 KP <sub>0</sub>	300 PSIG	2068 KP <sub>0</sub>
CONTENTS	WATER			

CUSTOMER:  
 LOCATION:  
 ENGINEER:  
 ORDER No.:  
 PROJECT/JOB:  
 LOCATION:  
 (QUOTE # )

TITLE G.A. 150 LB. WX SERIES HEAT EXCHANGERS	A R M S T R O N G				NUMBER WX-18-2P-2(8)	REV.
DATE: 12 / 01 / 94 BY: D.C.R.	TORONTO - CANADA TEL : (416) 755-2291	MONTREAL - CANADA TEL : (514) 421-2424	BUFFALO - N. Y. TEL : (716) 693-8813	COLCHESTER - U.K. TEL : (44) 120-657-9491		