



EXCHANGER SIZE *BAFFLE SPACING	DIMENSIONS											
	A		B		C		D		N1		N2	
	inches	mm	inches	mm	inches	mm	inches	mm	inches	mm	inches	mm
WX-204-2*-4	72 5/8	1845	30 1/2	775	15	381	53	1346	8	203	8	203
WX-205-2*-4	84 5/8	2149	42 1/2	1080	27	686	65	1651	8	203	8	203
WX-206-2*-4	96 5/8	2454	54 1/2	1384	39	991	77	1956	8	203	8	203
WX-207-2*-4	108 5/8	2759	66 1/2	1689	51	1295	89	2261	8	203	8	203
WX-208-2*-4	120 5/8	3064	78 1/2	1994	63	1600	101	2565	8	203	8	203
WX-209-2*-4	132 5/8	3369	90 1/2	2299	75	1905	113	2870	8	203	8	203
WX-2010-2*-4	144 5/8	3673	102 1/2	2604	87	2210	125	3175	8	203	8	203
WX-2011-2*-4	156 5/8	3978	114 1/2	2908	99	2515	137	3480	8	203	8	203
WX-2012-2*-4	168 5/8	4283	126 1/2	3213	111	2819	149	3785	8	203	8	203
WX-2013-2*-4	180 5/8	4588	138 1/2	3518	123	3124	161	4089	8	203	8	203
WX-2014-2*-4	192 5/8	4893	150 1/2	3823	135	3429	173	4394	8	203	8	203
WX-2015-2*-4	204 5/8	5197	162 1/2	4128	147	3734	185	4699	8	203	8	203

NOZZLE SCHEDULE				
SERVICE	MARK	SHELL SIDE	MARK	TUBE SIDE
INLET	N1	AS PER TABLE	N5	8 (203) FLG
OUTLET	N2	AS PER TABLE	N6	8 (203) FLG
DRAIN	N3	1/2 (13) NPT		
VENT	N4	3/4 (19) NPT		

- NOTES: 1. SUPPORTS SUPPLIED ONLY IF SPECIFIED ON ORDER.
 2. NOZZLE SIZES SHOWN ARE RECOMMENDED FOR MAXIMUM EXCHANGER LIFE.
 3. FABRICATED TO ASME CODE SECTION VIII DIVISION 1 AND LATEST ADDENDA.
 4. DRAWING IS NOT TO SCALE.
 5. ALL DIM'S ±1/8 (3) UNLESS OTHERWISE SHOWN.

DESIGN CONDITIONS				
	SHELL		TUBES	
DESIGN PRESSURE	150 PSIG	1034 KPa	150 PSIG	1034 KPa
DESIGN TEMPERATURE	375 °F	191 °C	375 °F	191 °C
MIN. DESIGN METAL TEMP.	40 °F	4.4 °C	40 °F	4.4 °C
HYDRO. TEST PRESSURE	225 PSIG	1551 KPa	225 PSIG	1551 KPa
CONTENTS	WATER		WATER	

CUSTOMER:
 LOCATION:
 ENGINEER:
 ORDER No.:
 PROJECT/JOB:
 LOCATION:
 TAG: (QUOTE #)

TITLE	G.A. 150 LB. WX SERIES HEAT EXCHANGERS				A R M S T R O N G				NUMBER	WX-20-2P-4(8)	REV.				
DATE:	12 / 01 / 94	BY:	D.C.R.	TORONTO - CANADA	MONTREAL - CANADA	BUFFALO - N. Y.	COLCHESTER - U.K.	TEL :	(416) 755-2291	TEL :	(514) 421-2424	TEL :	(716) 693-8813	TEL :	(44) 120-657-9491