



EXCHANGER SIZE *-BAFFLE SPACING	DIMENSIONS											
	A		B		C		D		(N1)		(N2)	
	inches	mm	inches	mm	inches	mm	inches	mm	inches	mm	inches	mm
WX-204-4*-1	59 1/4	1505	30 1/2	775	15	381	53	1346	8	203	8	203
WX-205-4*-1	71 1/4	1810	42 1/2	1080	27	686	65	1651	8	203	8	203
WX-206-4*-1	83 1/4	2115	54 1/2	1384	39	991	77	1956	8	203	8	203
WX-207-4*-1	95 1/4	2419	66 1/2	1689	51	1295	89	2261	8	203	8	203
WX-208-4*-1	107 1/4	2724	78 1/2	1994	63	1600	101	2565	8	203	8	203
WX-209-4*-1	119 1/4	3029	90 1/2	2299	75	1905	113	2870	8	203	8	203
WX-2010-4*-1	131 1/4	3334	102 1/2	2604	87	2210	125	3175	8	203	8	203
WX-2011-4*-1	143 1/4	3639	114 1/2	2908	99	2515	137	3480	8	203	8	203
WX-2012-4*-1	155 1/4	3943	126 1/2	3213	111	2819	149	3785	8	203	8	203
WX-2013-4*-1	167 1/4	4248	138 1/2	3518	123	3124	161	4089	8	203	8	203
WX-2014-4*-1	179 1/4	4553	150 1/2	3823	135	3429	173	4394	8	203	8	203
WX-2015-4*-1	191 1/4	4858	162 1/2	4128	147	3734	185	4699	8	203	8	203

NOZZLE SCHEDULE				
SERVICE	MARK	SHELL SIDE	MARK	TUBE SIDE
INLET	(N1)	AS PER TABLE	(N5)	6 (152) NPT
OUTLET	(N2)	AS PER TABLE	(N6)	6 (152) NPT
DRAIN	(N3)	1/2 (13) NPT	(N7)	1/2 (13) NPT
VENT	(N4)	3/4 (19) NPT		

NOTES: 1. SUPPORTS SUPPLIED ONLY IF SPECIFIED ON ORDER.  
 2. NOZZLE SIZES SHOWN ARE RECOMMENDED FOR MAX. EXCHANGER LIFE, NO EXTERNAL FORCES APPLY.  
 3. FABRICATED TO ASME CODE SECTION VIII DIVISION 1 AND LATEST ADDENDA.  
 4. DRAWING IS NOT TO SCALE.  
 5. ALL DIMN'S ±1/8 (3) UNLESS OTHERWISE SHOWN.

DESIGN CONDITIONS				
	SHELL		TUBES	
DESIGN PRESSURE	150 PSIG	1034 KPa	125 PSIG	862 KPa
DESIGN TEMPERATURE	375 °F	191 °C	375 °F	191 °C
MIN. DESIGN METAL TEMP.	40 °F	4.4 °C	40 °F	4.4 °C
HYDRO. TEST PRESSURE	225 PSIG	1551 KPa	250 PSIG	1723 KPa
CONTENTS	WATER		WATER	

CUSTOMER:  
 LOCATION:  
 ENGINEER:  
 ORDER No.:  
 PROJECT/JOB:  
 LOCATION:  
 TAG: (QUOTE # )

TITLE G.A. 150 LB. WX SERIES HEAT EXCHANGERS	A R M S T R O N G				NUMBER WX-20-4P-1(8)	REV. A 2001 J.R.
DATE: 12 / 01 / 94 BY: D.C.R.	TORONTO - CANADA TEL: (416) 755-2291	MONTREAL - CANADA TEL: (514) 421-2424	BUFFALO - N. Y. TEL: (716) 893-8813	COLCHESTER - U.K. TEL: (44) 120-657-9491		