



DIMENSIONS SHOWN AS: inches (mm)

2 - 3/4 (19) DIA. HOLES (TYP.)

EXCHANGER SIZE *-BAFFLE SPACING	DIMENSIONS											
	A		B		C		D		N1		N2	
	inches	mm	inches	mm	inches	mm	inches	mm	inches	mm	inches	mm
WX-62-2*-1	29 7/8	759	16	406	7	178	26	660	2	51	2	51
WX-63-2*-1	41 7/8	1064	28	711	19	483	38	965	2	51	2	51
WX-64-2*-1	53 7/8	1368	40	1016	31	787	50	1270	2	51	2	51
WX-65-2*-1	65 7/8	1673	52	1321	43	1092	62	1575	2	51	2	51
WX-66-2*-1	77 7/8	1978	64	1626	55	1397	74	1880	2	51	2	51
WX-67-2*-1	89 7/8	2283	76	1930	67	1702	86	2184	2	51	2	51
WX-68-2*-1	101 7/8	2588	88	2235	79	2007	98	2489	2	51	2	51
WX-69-2*-1	113 7/8	2892	100	2540	91	2311	110	2794	2	51	2	51
WX-610-2*-1	125 7/8	3197	112	2845	103	2616	122	3099	2	51	2	51
WX-611-2*-1	137 7/8	3502	124	3150	115	2921	134	3404	2	51	2	51
WX-612-2*-1	149 7/8	3807	136	3454	127	3226	146	3708	2	51	2	51

NOZZLE SCHEDULE

SERVICE	MARK	SHELL SIDE	MARK	TUBE SIDE
INLET	N1	AS PER TABLE	N5	2 (51) NPT
OUTLET	N2	AS PER TABLE	N6	2 (51) NPT
DRAIN	N3	1/2 (13) NPT		
VENT	N4	3/4 (19) NPT		

- NOTES:**
1. SUPPORTS SUPPLIED ONLY IF SPECIFIED ON ORDER.
 2. NOZZLE SIZES SHOWN ARE RECOMMENDED FOR MAXIMUM EXCHANGER LIFE.
 3. FABRICATED TO ASME CODE SECTION VIII DIVISION 1 AND LATEST ADDENDA.
 4. DRAWING IS NOT TO SCALE.
 5. ALL DIMN'S ±1/8 (3) UNLESS OTHERWISE SHOWN.

DESIGN CONDITIONS

	SHELL		TUBES	
DESIGN PRESSURE	150 PSIG	1034 KPa	150 PSIG	1034 KPa
DESIGN TEMPERATURE	375 °F	191 °C	375 °F	191 °C
MIN. DESIGN METAL TEMP.	35 °F	1.7 °C	35 °F	1.7 °C
HYDRO. TEST PRESSURE	225 PSIG	1551 KPa	300 PSIG	2068 KPa
CONTENTS	WATER		WATER	

CUSTOMER:

LOCATION:

ENGINEER:

ORDER No.:

PROJECT/JOB:

LOCATION:

TAG:

(QUOTE #)

TITLE	G.A. 150 LB. WX SERIES HEAT EXCHANGERS	A R M S T R O N G				NUMBER	WX-6-2P-1 (2)	REV.			
DATE:	12 / 01 / 94	BY:	D.C.R.	TEL :	(416) 755-2291	TEL :	(514) 421-2424	TEL :	(716) 693-8813	TEL :	(44) 120-657-9491