



DIMENSIONS SHOWN AS: inches (mm)

2 - $3/4$ (19) DIA. HOLES (TYP.)

EXCHANGER SIZE *-BAFFLE SPACING	DIMENSIONS											
	A		B		C		D		(N1)		(N2)	
	inches	mm	inches	mm	inches	mm	inches	mm	inches	mm	inches	mm
WX-62-2*-2	31 5/8	803	16	406	7	178	26	660	2	51	2	51
WX-63-2*-2	43 5/8	1108	28	711	19	483	38	965	2	51	2	51
WX-64-2*-2	55 5/8	1413	40	1016	31	787	50	1270	2	51	2	51
WX-65-2*-2	67 5/8	1718	52	1321	43	1092	62	1575	2	51	2	51
WX-66-2*-2	79 5/8	2022	64	1626	55	1397	74	1880	2	51	2	51
WX-67-2*-2	91 5/8	2327	76	1930	67	1702	86	2184	2	51	2	51
WX-68-2*-2	103 5/8	2632	88	2235	79	2007	98	2489	2	51	2	51
WX-69-2*-2	115 5/8	2937	100	2540	91	2311	110	2794	2	51	2	51
WX-610-2*-2	127 5/8	3242	112	2845	103	2616	122	3099	2	51	2	51
WX-611-2*-2	139 5/8	3546	124	3150	115	2921	134	3404	2	51	2	51
WX-612-2*-2	151 5/8	3851	136	3454	127	3226	146	3708	2	51	2	51

NOZZLE SCHEDULE

SERVICE	MARK	SHELL SIDE	MARK	TUBE SIDE
INLET	(N1)	AS PER TABLE	(N5)	2 (51) NPT
OUTLET	(N2)	AS PER TABLE	(N6)	2 (51) NPT
DRAIN	(N3)	1/2 (13) NPT		
VENT	(N4)	3/4 (19) NPT		

- NOTES: 1. SUPPORTS SUPPLIED ONLY IF SPECIFIED ON ORDER.
 2. NOZZLE SIZES SHOWN ARE RECOMMENDED FOR MAXIMUM EXCHANGER LIFE.
 3. FABRICATED TO ASME CODE SECTION VIII DIVISION 1 AND LATEST ADDENDA.
 4. DRAWING IS NOT TO SCALE.
 5. ALL DIMN'S $\pm 1/8$ (3) UNLESS OTHERWISE SHOWN.

DESIGN CONDITIONS

	SHELL		TUBES	
	DESIGN PRESSURE	150 PSIG	1034 KPa	150 PSIG
DESIGN TEMPERATURE	375 °F	191 °C	375 °F	191 °C
MIN. DESIGN METAL TEMP.	35 °F	1.7 °C	35 °F	1.7 °C
HYDRO. TEST PRESSURE	225 PSIG	1551 KPa	300 PSIG	2068 KPa
CONTENTS	WATER		WATER	

CUSTOMER:

LOCATION:

ENGINEER:

ORDER No.:

PROJECT/JOB:

LOCATION:

TAG:

(QUOTE #)

TITLE	G.A. 150 LB. WX SERIES HEAT EXCHANGERS	A R M S T R O N G				NUMBER	WX-6-2P-2 (2)	REV.	
DATE:	12 / 01 / 94	BY:	D.C.R.	TEL: (416) 755-2291	TEL: (514) 421-2424	TEL: (716) 693-8813	TEL: (44) 120-657-9491		