

## DESIGN ENVELOPE 6800 G | COMMERCIAL WATER BOOSTER | I220402 - I120402s | SUBMITTAL

File No: 106.0003IEC  
Date: APRIL 24, 2018  
Supersedes: NEW  
Date: NEW

Job: \_\_\_\_\_ Representative: \_\_\_\_\_  
 \_\_\_\_\_ Order by: \_\_\_\_\_ Date: \_\_\_\_\_  
 Engineer: \_\_\_\_\_ Submitted by: \_\_\_\_\_ Date: \_\_\_\_\_  
 Contractor: \_\_\_\_\_ Approved by: \_\_\_\_\_ Date: \_\_\_\_\_

### PUMP DESIGN DATA

No. of pumps: 2 Tag: \_\_\_\_\_ Series: 4700  
 Total package capacity: \_\_\_\_\_ L/s (m<sup>3</sup>/h)  
 Pump capacity: \_\_\_\_\_ L/s (m<sup>3</sup>/h)  
 Head: \_\_\_\_\_ Bar (m) Liquid: \_\_\_\_\_  
 Construction: Stainless steel 304

### CONNECTION ORIENTATION

Suction  Right\*  Left\*  
 Discharge  Right\*  Left\*

\* When facing control panel

### DRIVE DATA

Enclosure: IP66  
 EMI/RFI control: Integrated filter designed to meet EN61800-3  
 Harmonic suppression: Integrated DC link reactors  
 Cooling: Fan-cooled through back channel  
 Ambient temperature: -10°C to +45°C up to 1000 meters

### OPTIONAL EQUIPMENT

Duty standby discharge transducer:  Yes  No  
 BMS communication:  BACnet MS/TP  BACnet IP  
 LonWorks  
 Float switch:  Yes  No  
 AV kit:  No  Potable water untied  
 Potable water tied  
 Overhead break tank:  Yes  No

### SYSTEM CONSTRUCTION DATA

System description: Duplex  
 Model: \_\_\_\_\_  
 Header connections: Flanged  
 Piping material: Stainless steel 304  
 Valve type: Ball valve/butterfly valve and Check valve  
 Setup:  All duty  Duty standby

### MOTOR DESIGN DATA

kW: 1.1 RPM: 3600 Frame size: 90S Enclosure: TEFC  
 Power supply: 400/3/50 V Efficiency: IE5


### CONTROL PANEL SPECIFICATIONS

Enclosure rating: IP55  
 HMI: Colour touch screen  
 Low suction shutdown  
 Main disconnect with interlock  
 Fused motor protection  
 Power on indication  
 Motor run indication  
 No-flow shutdown and automatic alternation  
 Soft fill mode  
 Pressure setback mode  
 Field adjustable set points, alarms  
 Flash memory storage  
 Suction transducer included  
 Modbus RTU serial communication

### DESIGN ENVELOPE CAPABILITY DATA


ENVELOPE CURVE NUMBER	PUMP	PRESSURE RATING in bar	MAX WORKING PRESSURE in bar	EACH MOTOR in kW	SUCTION E	DISCHARGE F	FLC in Amps	
<input type="checkbox"/> I220402	<input type="checkbox"/> I120402S	VMS-04:04	PN16	4.90	1.1	DN 50	DN 50	2.3

I220402



Water, spgr= 1.0000

I120402S



Water, spgr= 1.0000

DIMENSION DATA

I220402 I120402S

<b>A:</b>	710 (27.95)
<b>B:</b>	1560 (61.42)
<b>C:</b>	706 (27.81)
<b>D:</b>	500 (19.68)
<b>G:</b>	140 (5.51)
<b>H:</b>	314 (12.36)
<b>J:</b>	343 (13.50)
<b>K:</b>	657 (25.87)
<b>L:</b>	822 (32.36)
<b>M:</b>	620 (24.41)
<b>N:</b>	363 (14.29)
<b>P:</b>	328 (12.91)
<b>R:</b>	390 (15.35)
<b>T:</b>	130 (5.12)
<b>WEIGHT:</b>	234.0 (516)

Dimensions - mm (inches)

Weight - kg (lbs)

**Note:** Tolerances are 12 mm ( $\pm 1/2"$ ) unless otherwise specified.

TORONTO  
+1 416 755 2291

BUFFALO  
+1 716 693 8813

BIRMINGHAM  
+44 (0) 8444 145 145

MANCHESTER  
+44 (0) 8444 145 145

BANGALORE  
+91 (0) 80 4906 3555

SHANGHAI  
+86 (0) 21 5237 0909

SÃO PAULO  
+55 11 4781 5500

