

EE-W10 | ENTERPRISE ENVELOPE FOR WATER-COOLED CHILLER PLANT OPTIMIZATION | SUBMITTAL

File No: 90.7653
 Date: DECEMBER 17, 2024
 Supersedes: NEW
 Date: NEW

Job: _____ Representative: _____
 _____ Order no.: _____ Date: _____
 Engineer: _____ Submitted by: _____ Date: _____
 Contractor: _____ Approved by: _____ Date: _____

PLANT CONFIGURATION - HEADERED

WATER COOLED CHILLERS*				COOLING TOWERS**		
QUANTITY	# GROUPS	QUANTITY PER GROUP	CAPACITY (TONS) PER CHILLER	# GROUPS	QUANTITY	
					<input type="checkbox"/> NO TOWERMAX	<input type="checkbox"/> WITH TOWERMAX
<input type="checkbox"/> 1	<input type="checkbox"/> 1	1		1	1	<input type="checkbox"/> 1 <input type="checkbox"/> 2 and <input type="checkbox"/> 3
<input type="checkbox"/> 2	<input type="checkbox"/> 1	2		1	2	<input type="checkbox"/> 1 <input type="checkbox"/> 2 and <input type="checkbox"/> 3
	<input type="checkbox"/> 2	Grp A: 1 Grp B: 1	Group A: _____ Group B: _____	<input type="checkbox"/> 1 <input type="checkbox"/> 2	1 Grp A: 1 Grp B: 1	<input type="checkbox"/> 1 <input type="checkbox"/> 2 and <input type="checkbox"/> 3 Grp A: __ (1 to 2) + Grp B: __ (1 to 2) ≤ 3
<input type="checkbox"/> 3	<input type="checkbox"/> 1	3		1	3	<input type="checkbox"/> 1 <input type="checkbox"/> 2 and <input type="checkbox"/> 3
	<input type="checkbox"/> 2	Grp A: 2 Grp B: 1	Group A: _____ Group B: _____	<input type="checkbox"/> 1 <input type="checkbox"/> 2	3 2	<input type="checkbox"/> 1 <input type="checkbox"/> 2 and <input type="checkbox"/> 3 Grp A: __ (1 to 2) + Grp B: __ (1 to 2) ≤ 3
	<input type="checkbox"/> 3	Grp A: 1 Grp B: 1 Grp C: 1	Group A: _____ Group B: _____ Group C: _____	<input type="checkbox"/> 1 <input type="checkbox"/> 3	3 Grp A: 1 / Grp B: 1 / Grp C: 1	<input type="checkbox"/> 1 <input type="checkbox"/> 2 and <input type="checkbox"/> 3 Grp A: __ (1) + Grp B: __ (1) + Grp C: __ (1) ≤ 3

NOTES:

- * Only identical chillers can be grouped together; Group A, Group B & Group C operate singly
- ** Only headered cooling towers are allowed. 1 speed signal/VFD is considered per tower; only identical cooling towers can be grouped together. Cooling towers in Group A, Group B and Group C associates with chillers in Group A, Group B and Group C accordingly

PLANT CONFIGURATION - HEADERED

PUMP TYPE	# DUTY PUMPS = # CHILLERS	# CHILLER GROUPS	# CHILLER PER GROUP	PRIMARY CHW PUMPS*/***			CONDENSER CW PUMPS*/***		
				# PUMP GROUPS	# PUMP PER GROUP	STANDBY PUMPS**	# PUMP GROUPS	# PUMP PER GROUP	STANDBY PUMPS**
<input type="checkbox"/> Single	<input type="checkbox"/> 1	1	1	1	1	<input type="checkbox"/> Yes (+1) <input type="checkbox"/> No (0)	1	1	<input type="checkbox"/> Yes (+1) <input type="checkbox"/> No (0)
	<input type="checkbox"/> 2	1	2	<input type="checkbox"/> 1	2	<input type="checkbox"/> Yes (+1) <input type="checkbox"/> No (0)	<input type="checkbox"/> 1	2	<input type="checkbox"/> Yes (+1) <input type="checkbox"/> No (0)
		2	Grp A: 1 Grp B: 1	<input type="checkbox"/> 1	2	<input type="checkbox"/> Yes (+1) <input type="checkbox"/> No (0)	<input type="checkbox"/> 1	2	<input type="checkbox"/> Yes (+1) <input type="checkbox"/> No (0)
	<input type="checkbox"/> 2			Grp A: 1 Grp B: 1	<input type="checkbox"/> Yes (+1) <input type="checkbox"/> No (0) <input type="checkbox"/> Yes (+1) <input type="checkbox"/> No (0)	<input type="checkbox"/> 2	Grp A: 1 Grp B: 1	<input type="checkbox"/> Yes (+1) <input type="checkbox"/> No (0) <input type="checkbox"/> Yes (+1) <input type="checkbox"/> No (0)	
	<input type="checkbox"/> 3	1	3	<input type="checkbox"/> 1	3	No	<input type="checkbox"/> 1	3	No
		2	Grp A: 2 Grp B: 1	<input type="checkbox"/> 1	3		<input type="checkbox"/> 1	3	
		2		<input type="checkbox"/> 2	Grp A: 2 Grp B: 1		<input type="checkbox"/> 2	Grp A: 2 Grp B: 1	
		3	Grp A: 1 Grp B: 1 Grp C: 1	<input type="checkbox"/> 1	3		<input type="checkbox"/> 1	3	
	3	Grp A: 1 Grp B: 1 Grp C: 1	<input type="checkbox"/> 3	Grp A: 1 Grp B: 1 Grp C: 1	<input type="checkbox"/> 3		Grp A: 1 Grp B: 1 Grp C: 1		

NOTES:

* Both chw Pumps & cw Pumps must be same configuration (headered)

** Total number of chw or cw pumps (i.e. Duty + Standby) ≤ 3

*** Only identical pumps can be grouped together; chw Pumps & cw Pumps in Group A, Group B & Group C associate with chillers in Group A, Group B & Group C accordingly

PLANT CONFIGURATION - DEDICATED

WATER COOLED CHILLERS*					COOLING TOWERS**	
QUANTITY	CHILLERS TYPE	# GROUPS	CAPACITY (TONS) PER CHILLER	GROUPING OF CHILLERS	# GROUPS	QUANTITY
<input type="checkbox"/> 1	Identical	1	Chiller 1: _____	N/A	1	1
<input type="checkbox"/> 2	Identical	<input type="checkbox"/> 1	Chiller 1: _____ Chiller 2: _____	N/A	1	2
	Mixed	<input type="checkbox"/> 1 <input type="checkbox"/> 2		Chiller 1: <input type="checkbox"/> Grp A <input type="checkbox"/> Grp B <input type="checkbox"/> Common Chiller 2: <input type="checkbox"/> Grp A <input type="checkbox"/> Grp B <input type="checkbox"/> Common		
<input type="checkbox"/> 3	Identical	<input type="checkbox"/> 1	Chiller 1: _____ Chiller 2: _____ Chiller 3: _____	N/A	1	3
	Mixed	<input type="checkbox"/> 1		N/A		
		<input type="checkbox"/> 2 <input type="checkbox"/> 3		Chiller 1: <input type="checkbox"/> Grp A <input type="checkbox"/> Grp B <input type="checkbox"/> Grp C <input type="checkbox"/> Common Chiller 2: <input type="checkbox"/> Grp A <input type="checkbox"/> Grp B <input type="checkbox"/> Grp C <input type="checkbox"/> Common Chiller 3: <input type="checkbox"/> Grp A <input type="checkbox"/> Grp B <input type="checkbox"/> Grp C <input type="checkbox"/> Common		

NOTES:

* Groups A, B & C operate singly; Common always available to all Groups

** Only headered & identical cooling towers are allowed; 1 speed signal/VFD is considered per tower

PLANT CONFIGURATION - DEDICATED

TYPE	QUANTITY OF PRIMARY CHW PUMPS*	QUANTITY OF CONDENSER CW PUMPS*
<input type="checkbox"/> Single	Duty Pumps = Quantity of Chillers	Duty: ___(1 to 3) + 0 Standby
<input type="checkbox"/> dualArm		Duty: ___(1 to 3) + 0 Standby**
<input type="checkbox"/> Tango		Duty: ___(1 to 3) + 0 Standby**
<input type="checkbox"/> Twin		Duty: ___(1 to 3)***

NOTES:

- * Both CHW Pumps & CW Pumps must be same configuration (dedicated)
- ** 1 dualArm or Tango = 2 rotating assemblies (considered Duty/Duty)
- *** 1 Twin = 2 rotating assemblies (considered Duty/Standby)

STANDARD FUNCTIONALITY AND CONSTRUCTION

The Armstrong EE-W10 is a pre-programmed optimization system designed for water-cooled variable primary chiller plant. It is supplied with all hardware, software and programming required to sequence and optimize the following equipment for better efficiency of the overall chiller plant:

- Up to three (3) water-cooled chillers
- Up to three (3) variable speed chilled water pumps in headered or dedicated configuration
- Up to three (3) variable speed condenser water pumps in headered or dedicated configuration
- Up to three (3) cooling towers with variable speed fans
- Associated isolation and by-pass valves

Standard construction

- Multi-colour 10" back-lit touchscreen (not to be directly exposed to sunlight)
- Internal circuit breaker protection
- One (1) NEMA 4 rated panel
- Secure front cabinet door with lock and key

Standard functionality

- Remote or local start/stop mode of operation
- Three level password security
 - Level 0 view only
 - Level 1 operator view (for equipment operation and field adjustment)
 - Level 2 installer view (for factory/commissioning)
- Selectable on-screen languages: English, French, Korean, Portuguese, Simplified Chinese, Spanish and Traditional Chinese

- Automatic sequencing and alternation, using dynamic compensation of performance mapped chillers, pumps and cooling towers:
 - In headered configuration, automate up to 3 sizes/types of chillers, pumps and cooling tower
 - In dedicated configuration, automate up to 3 sizes/types of chillers and pumps
 - In both configurations, form up to 3 groups of each type of equipment and operate based on a scheduler
- Obtain system flow from flow meter or from Design Envelope pumps' sensorless reading
- Sensorless pump speed control of Design Envelope pumps (Single, dualArm, Tango or Twin) and Parallel Sensorless™ sequencing with best efficiency point staging if pumps are in headered configuration
- Manual or automatic control system (H-O-A selection)
- On-screen menu driven operator interface with:
 - Active-element schematic displays with links to sub-menus for additional plant equipment information
 - Real time display of the efficiencies of plant and individual components, and the overall plant heat balance calculation
 - Dynamic overview of the hydronic circuit indicating piping configuration
 - Detailed view of each connected piece of equipment
 - Overview of 1 zones with actual reading, setpoint, status and deviation of individual zone
 - Capability to view and modify parameters and setpoints of all connected equipment, valves and sensors, and to override equipment operating mode
 - Adjustable PID parameters to control pump speed, bypass valves and cooling valves (ASHRAE 90.1 compliance)

4

- Separate displays to view all available live and historical data, including alarms and trends, which can also be downloaded as a csv file
- Standard Modbus RTU communication between EE-W10 controller and VFD's (pumps and towers)
- Enable auxiliary equipment through dry contact output for water treatment
- Performance management service on annual subscription.

Input/Output

- A point schedule detailing analog and digital input and output points description, functions and types for the following:

Digital inputs

- Chilled and condenser water isolation valves open & close feedback
- Cooling tower inlet & outlet isolation valves open & close feedback

Digital outputs

- Open & close chilled water isolation valves
- Condenser water isolation valves control
- Cooling tower inlet & outlet isolation valves control

Analog inputs

- Zone differential pressure or zone temperature signals (1) (4-20mA)
- Supply and return temperatures for chilled and condenser water (4-20mA)
- Chilled water and condenser water flow sensors (4-20mA)
- Chilled water and cooling tower bypass valves position feedback (0-10VDC)
- Chiller current/kW sensors (4-20mA)
- Outside air temperature and humidity (4-20mA)

Analog outputs

- Chilled water and cooling tower bypass valves control (0-10VDC)
- Standard communication with pumps and cooling tower fans through serial Modbus protocol
- Optional communication port for interfacing with a BAS
- One terminal block for power supply 100-240 Vac/
1 Ph/50-60 Hz

General sequence of operation

- All plant control system settings, including the number of chillers, cooling towers and pumps, as well as how they are connected (headered or dedicated) shall be able to modify at the graphic user interface (GUI) after entering the appropriate password.

- The plant control system shall determine the most energy efficient combination of operating primary pumps and pump operating speed by Parallel Sensorless™ sequencing with best efficiency point staging, or adjusts the pump speed to maintain the differential pressure or temperature at one zone at or above setpoint, while maintaining within equipment upper and lower flow limits and meeting system cooling load.
- The plant control system shall continuously monitor all zone signals to determine an active control zone. Use of a multiplexer for multiple sensor inputs is not acceptable.
- The plant control system shall automatically disable any zone differential pressure/temperature signals that are not within limits and alert the operator of a possible transmitter failure. If system found all differential pressure/temperature sensors failure in the building, the pump speed will default to a pre-defined percentage of full speed (factory default loaded as 95% of full speed).
- The plant control system shall sequence the pumps based on a field adjustable interval of operating days with a BUMP-LESS transfer algorithm. The control system incorporates an adjustable PID control loop and embedded logic to prevent hunting, pump flow surge and motor overloading.
- To meet ASHRAE 90.1 requirement, the plant control system shall obtain the position of the most open cooling valve from the BAS and maintain this valve position at 95% by a PID loop.
- The plant control system shall determine the optimum numbers of pumps, chillers and cooling towers to operate based on the plant load (thermal energy rejected) or to prevent the flow through the running chillers to exceed their rated maximum (or fall below their minimum), or to exceed the power consumed by the running chillers to exceed their rated maximum, or to prevent the supply temperature to exceed the setpoint by a field adjustable offset.
- For each chiller the plant control system has an adjustable field to enter its capacity. The plant load (in Tons and %) is displayed on the touch screen display and used to Stage On and Off the chillers, in conjunction with the other conditions explained in the previous paragraph.
- The plant control system shall rotate the lead chiller, lead pump and lead cooling tower on field adjustable intervals of operating days. Should any chiller, VFD/pump or cooling tower fail, the plant control system will trigger the corresponding alarm and remove said equipment from the auto sequence and rotation. In place of the failed equipment, the next available chiller, pump or cooling tower shall be operated.

- The plant control system shall be capable of scheduling the operation of pumps, towers and chillers by time and date to suit local circumstances.
- The chilled water setpoint shall be determined by one of the three options: manual entry on the GUI, calculated based on the outdoor air temperature, or provided by an external optimization module or the BAS. The plant control system shall be capable of scheduling the operation of pumps, towers and chillers by time and date to suit local circumstances.
- The plant control system shall alert the operator if any of the return temperature sensors, supply temperature sensors or flow sensors failed, and maintain the number of chillers in operation (no stage on or off) until the alarm is cleared.
- Even if no chillers are running, as long as the plant control system is enabled, one pump shall be operated to circulate water.
- The plant control system shall be capable of interfacing with up to 3 chilled water isolation valves and up to 3 condenser water isolation valves. A digital output opens and closes the valves, and a digital input provides open/close feedback.
- The plant control system shall modulate the bypass valves to maintain the minimum chilled water flow and minimum entering condenser water temperature required by the operating chillers.
- The plant control system shall determine the optimized cooling tower fan speed, within a field adjustable range, to maintain the entering condenser water temperature at setpoint.
- The plant control system shall be capable of operating up to 3 chillers of different sizes or types with the following conditions:
 - A** If the chilled water pumps are in headered configuration, there can be 3 sizes or 3 types of chillers; up to 3 chiller groups can be formed with the condition that only identical chillers (i.e. make & model, size, minimum flow, etc.) can be grouped together.
 - B** If the chilled water pumps are in dedicated configuration, there can be up to 3 sizes or 3 types of chillers; up to 3 chiller groups can be formed
 - C** Chilled water pumps and condenser water pumps must have the same configuration (i.e. either both headered or both dedicated)
- In headered configuration, the plant control system shall allow up to 3 pump groups to be formed if there are 3 chiller groups available, with the condition that only identical pumps (i.e. same make & model, flow, head, etc.) shall be grouped together. Each pump group is associated with the corresponding chiller group, and only pumps in the active pump group is enabled and staged. 1 pump in each pump group shall be allowed as stand-by.
- In headered configuration, the plant control system shall allow up to 3 cooling tower groups to be formed if there are 3 chiller groups available, with the condition that only identical cooling towers (i.e. make & model, size, minimum flow, etc.) shall be grouped together. Each cooling tower group is associated with the corresponding chiller group and only cooling towers in the active cooling tower group is enabled and staged.
- In dedicated configuration, all cooling towers must be identical.
- To operate different sizes/types of chillers, the plant control system shall determine which group of chillers to operate based on either a digital input or a scheduler configurable via the GUI. Only chillers in the active chiller group, and its associated pumps and cooling towers group, shall be enabled and staged.
- When the TowerMax™ energy saving optimization module to upgrade efficiencies of the condenser water circuit is enabled, it shall override the sequencing logic of condenser water pumps and cooling towers and provides optimized operation.
- Automatic operation mode: the plant control system shall include each of the chillers, pumps and cooling towers that are set in automatic operation mode in the sequence and modulate these equipment automatically to meet the current cooling load with optimum operating efficiency.
- Manual operation mode (for commissioning): When any chillers, pumps or cooling towers is switched to the manual operation mode by the operator, the operation of such equipment shall continue at the same status when operation mode was switched to manual mode until further changes by the operator. The plant control system shall exclude equipment in manual mode from the automatic operation or sequencing. When operation mode is switched back to auto, the automatic operation mode shall be resumed.


OPTIONAL FEATURES AND DIMENSIONS

CHILLER COMMUNICATION		DIMENSIONS AND WEIGHTS				
		LENGTH	HEIGHT	DEPTH	WEIGHT	ENCLOSURE
Interface	<input type="checkbox"/> Modbus RTU <input type="checkbox"/> BACnet™	30.0 (762)	24.0 (610)	8.8 (223)	75 (34)	NEMA <input type="checkbox"/> Type 4*
Hardwired (Output 0-10V)	<input type="checkbox"/>					
Hardwired (Output 4-20 mA)	<input type="checkbox"/>					

Notes:

- Dimensions in inches (mm) Weights in lbs (kg)
- Weights are approximate

* NEMA 4X recommended for outdoor application. Comprises of a stainless steel panel enclosure and a transparent non-metallic hinged inspection window protecting the screen.



HIGHLIGHTS

- TowerMax™ plant optimization module, included in the first year subscription of ECO*PULSE performance management service. Internet connection required. TowerMax™ deactivates when ECO*PULSE subscription lapses
- ECO*PULSE performance management service is on a subscription basis. Internet connection required)
- Export crating
- On-site start up by 1 trained Armstrong service provider.

BAS COMMUNICATION

- Not required
- Modbus RTU
- Modbus TCP
- BACnet™ MS/TP
- BACnet™ IP

PANEL APPROVAL

- UL (Standard)
- CSA
- CE

INSTRUMENTATION (FOR THE PUMP CONTROL)	TOTAL QUANTITY	FOR PRIMARY PUMP SPEED CONTROL			
		SENSORLESS	LOCAL PLANT DP	ZONE DP	ZONE RETURN TEMP
<input type="checkbox"/> Zone dP sensors		N/A	N/A	= qty of zones	N/A
<input type="checkbox"/> Zone return temperature sensors		N/A	N/A	N/A	= qty of zones

INSTRUMENTATION (FOR THE SYSTEM)	TOTAL QUANTITY	RECOMMENDED
<input type="checkbox"/> Primary flow sensor*		1
<input type="checkbox"/> Primary supply and return temperature sensors		2
<input type="checkbox"/> Chiller kW sensors**		= qty of chillers
<input type="checkbox"/> Condenser temperature sensors		2
<input type="checkbox"/> Condenser flow sensor*		1
<input type="checkbox"/> Outside air temperature & humidity sensor		1

* Not required with Design Envelope pumps

** Optional if each chiller already has an integrated kW reading

TORONTO

23 BERTRAND AVENUE,
TORONTO, ONTARIO,
CANADA, M1L 2P3
+1 416 755 2291

BUFFALO

93 EAST AVENUE, NORTH
TONAWANDA, NEW YORK,
USA, 14120-6594
+1 716 693 8813

DROITWICH SPA

POINTON WAY, STONEBRIDGE CROSS
BUSINESS PARK, DROITWICH SPA,
WORCESTERSHIRE,
UNITED KINGDOM, WR9 0LW
+44 121 550 5333

MANCHESTER

WOLVERTON STREET, MANCHESTER
UNITED KINGDOM, M11 2ET
+44 161 223 2223

BANGALORE

#18, LEWIS WORKSPACE, 3RD FLOOR,
OFF MILLERS - NANDIDURGA ROAD,
JAYAMAHAL CBD, BENSON TOWN,
BANGALORE, INDIA 560 046
+91 80 4906 3555

SHANGHAI

UNIT 903, 888 NORTH SICHUAN RD.
HONGKOU DISTRICT, SHANGHAI
CHINA, 200085
+86 21 5237 0909

BEIJING

ROOM 1612, NANYIN BUILDING NO.2
NORTH EAST THRID RING ROAD
CHAOYANG DISTRICT, BEIJING,
CHINA 100027
+86 21 5237 0909

SÃO PAULO

RUA JOSÉ SEMIÃO RODRIGUES
AGOSTINHO, 1370 GALPÃO 6 EMBU
DAS ARTES, SAO PAULO, BRAZIL
+55 11 4785 1330

LYON

93 RUE DE LA VILLETTE
LYON, 69003 FRANCE
+33 4 20 10 26 21

DUBAI

JAFZA VIEW 19, OFFICE 402
P.O.BOX 18226 JAFZA,
DUBAI - UNITED ARAB EMIRATES
+971 4 887 6775

JIMBOLIA

STR CALEA MOTILOR NR. 2C
JIMBOLIA 305400, JUD.TIMIS
ROMANIA
+40 256 360 030

FRANKFURT

WESTERBACHSTRASSE 32,
D-61476 KRONBERG IM TAUNUS
GERMANY
+49 6173 999 77 55

ARMSTRONG FLUID TECHNOLOGY®
ESTABLISHED 1934

ARMSTRONGFLUIDTECHNOLOGY.COM