

L SERIES | HYDRONIC EXPANSION TANKS | 35-L TO 130-L | SUBMITTAL

File No: 37.521
Date: MARCH 28, 2022
Supersedes: 37.521
Date: FEBRUARY 18, 2010

Job: _____ Representative: _____

Ordered by: _____ Date: _____
Engineer: _____ Submitted by: _____ Date: _____
Contractor: _____ Approved by: _____ Date: _____

DATA

Model no. ordered: _____ Qty: _____
Tag no.: _____ Charge pressure: _____ psi/kPa
Standard factory charge is 40 psi (276 kPa) unless otherwise specified.

MAXIMUM OPERATING CONDITIONS

Temperature Range: -20°F to 240°F (-29°C to 115.5°C)
Maximum Pressure: 125psi (862 kPa)

NOTES

- Not for Domestic Potable Water Systems.
- Designed and constructed per ASME, Section VIII, Division 1.
- California code sight-glass and seismic clips available as an option.
- Allow a minimum of 18" (457 mm) clearance for system piping.
- Mounting kit available on request.


MATERIALS OF CONSTRUCTION

Shell: Carbon steel
Bladder: Heavy Duty Butyl

TYPICAL SPECIFICATION

Furnish and install, as shown on the plans, Armstrong Model _____-L ASME pre-charged bladder Expansion Tank, stamped for _____ psi working pressure. Each tank will be supplied with a heavy duty butyl replaceable bladder. Tank shall be supplied with a ring base, lifting rings, and NPT system connection. An air charging valve connection (standard tire valve) shall be provided to facilitate adjusting pre-charge pressure to meet actual system conditions.

MODEL	TANK VOLUME in gal.(L)	DIMENSIONS in inches (mm)						SHIPPING WEIGHT in lbs(kg) 125PSI	
		A	B	SYSTEM CONNECTION NPT		CHARGING VALVE E	F		G
				C	D				
35-L	10 (38)	12.00 (305)	23.50 (597)	—	0.75 (19)	0.302"– 32NC	10.00 (254)	—	40 (18.1)
50-L	13 (49)	14.00 (356)	24.00 (610)	—	0.75 (19)		10.00 (254)	—	50 (22.7)
85-L	23 (87)	16.00 (406)	37.00 (940)	1.00 (25)	0.75 (19)		12.00 (305)	5.50 (140)	90 (40.8)
130-L	35 (132)	20.00 (508)	37.00 (940)	1.00 (25)	0.75 (19)		16.00 (406)	5.50 (140)	125 (56.7)



TORONTO
+1 416 755 2291

MODELS 35-L & 50-L

BUFFALO
+1 716 693 8813

DROITWICH SPA
+44 8444 145 145

MANCHESTER
+44 8444 145 145

BANGALORE
+91 80 4906 3555

SHANGHAI
+86 21 5237 0909


SÃO PAULO
+55 11 4785 1330

LYON
+33 4 26 83 78 74

DUBAI
+971 4 887 6775

MANNHEIM
+49 621 3999 9858

JIMBOLIA
+40 256 360 030



MODELS 85-L TO 130-L