

L SERIES HIGH PRESSURE | HYDRONIC EXPANSION

TANKS | 35-L TO 800-L | SUBMITTAL

File No: 37.522

Date: APRIL 05, 2022

Supersedes: 37.522

Date: JUNE 15, 2016

Job:	Representative:					
	Ordered by:	Date:				
Engineer:	Submitted by:	Date:				
Contractor:	Approved by:	Date:				
DATA	MATERIALS OF CO	NSTRUCTION				
Model no. ordered: Qty: psi/ Tag no.: Charge pressure: psi/ Optional California sight-glass and seismic clips: Yes Standard factory charge is 40 psi (276 kPa) unless otherwise spec	Bladder: Heavy Duty But System Connection: Carl					
MAXIMUM OPERATING CONDITIONS	TYPICAL SPECIFIC	TYPICAL SPECIFICATION				
Temperature Range: 40°F to 240°F (4.4°C to 115.5°C Maximum Pressure: ☐ 175 psi (1206 kPa) ☐ 250 psi (1724 kPa)	gallon" diamo pre-charged steel expans bladder. The tank shall ha 0.302"-32 charging valve to facilitate the on-site ch requirements. The tank n with most recent edition	Furnish and install, as shown on plans, a gallon " diameter x " (high) pre-charged steel expansion tank with heavy-duty butyl bladder. The tank shall have NPT system connections and a 0.302"-32 charging valve connection (standard tire valve) to facilitate the on-site charging of the tank to meet system requirements. The tank must be constructed in accordance with most recent edition of Section VIII Division 1 of the ASME Boiler and Pressure Vessel Code.				

DESCRIPTION

L series (High Pressure) Tanks are ASME removable bladder type pre-charged expansion tanks. They are designed to absorb the expansion forces and control the pressure in heating/cooling systems. The system's expanded water (fully compatible with water/glycol mixtures) is contained in a full acceptance heavy-duty butyl bladder that prevents tank corrosion and waterlogging problems. All L series expansion tanks can be installed vertically or horizontally.

NOTES

- Tanks are factory pre-charged at 40 psi and field adjustable.
- California code-sight glass is available upon request.
- Both top and bottom connections (c and D) access the bladder.
- Mounting kit available upon request

	TANK VOLUME in gal.(L)	DIMENSIONS in inches (mm)							ADDON GUIDANIG	
MODEL		A	В	SYSTEM CONNECTION NPT		CHARGING VALVE	F	G	APPROX. SHIPPING WEIGHT in lbs.(kg)	
				С	D	E			175PSI	250PSI
35-L	10 (38)	12.00	23.50	_	0.75	0.302"- 32NC	10.00		52	53
		(305)	(597)		(19)		(254)	_	(23.6)	(24.0)
50-L	13 (49)	14.00	24.00		0.75		10.00	_	59	65
		(356)	(610)		(19)		(254)		(26.8)	(29.5)
85-L	23 (87)	16.00	37.00	1.00	0.75		12.00	5.50	95	105
		(406)	(940)	(25)	(19)		(305)	(140)	(43.1)	(47.6)
130-L	35 (132)	20.00	37.00	1.00	0.75		16.00	5.50	127	141
		(508)	(940)	(25)	(19)		(406)	(140)	(57.6)	(63.9)
200-L	53 (200)	24.00	43.00	1.50	0.75		20.00	5.25	194	220
		(610)	(1092)	(38)	(19)		(508)	(133)	(88.0)	(99.8)
300-L	79 (300)	24.00	55.00	1.50	0.75		20.00	5.25	252	282
		(610)	(1397)	(38)	(19)		(508)	(133)	(114.3)	(127.9)
400-L	106 (400)	30.00	49.00	1.50	0.75		24.00	5.25	336	410
		(762)	(1245)	(38)	(19)		(610)	(133)	(152.4)	(186.0)
500-L	132 (500)	30.00	57.00	2.00	0.75		24.00	5.25	400	512
		(762)	(1448)	(51)	(19)		(610)	(133)	(181.4)	(232.2)
600-L	158 (600)	30.00	65.00	2.00	0.75		24.00	5.25	419	569
		(762)	(1651)	(51)	(19)		(610)	(133)	(190.0)	(258.1)
800-L	211 (800)	32.00	76.00	2.00	0.75		28.00	5.25	592	711
		(813)	(1930)	(51)	(19)		(711)	(133)	(268.5)	(322.5)



DROITWICH SPA +44 8444 145 145

MANCHESTER +44 8444 145 145

BANGALORE

+91 80 4906 3555

SHANGHAI

+86 21 5237 0909

são paulo +55 11 4785 1330

LYON

+33 4 26 83 78 74


 $\mathsf{D}\,\mathsf{U}\,\mathsf{B}\,\mathsf{A}\,\mathsf{I}$

+971 4 887 6775


 $\mathsf{MANNHEIM}$

+49 621 3999 9858

JIMBOLIA +40 256 360 030



MODELS 35-L & 50-L



MODELS 85-L TO 800-L

ARMSTRONG FLUID TECHNOLOGY ESTABLISHED 1934

ARMSTRONGFLUIDTECHNOLOGY.COM