



EXCHANGER SIZE	DIMENSIONS											
	A		B		C		D		N1		N2	
	inches	mm	inches	mm	inches	mm	inches	mm	inches	mm	inches	mm
WS-62-2E4	43 1/4	1099	23	584	15	381	25	635	1 1/2	38	1	25
WS-63-2E4	55 1/4	1403	35	889	27	686	37	940	2	51	1	25
WS-64-2E4	67 1/4	1708	47	1194	39	991	49	1245	2 1/2	64	1	25
WS-65-2E4	79 1/4	2013	59	1499	51	1295	61	1549	2 1/2	64	1	25
WS-66-2E4	91 1/4	2318	71	1803	63	1600	73	1854	3	76	1	25
WS-67-2E4	103 1/4	2623	83	2108	75	1905	85	2159	3	76	1	25
WS-68-2E4	115 1/4	2927	95	2413	87	2210	97	2464	3	76	1	25

NOZZLE SCHEDULE				
SERVICE	MARK	SHELL SIDE	MARK	TUBE SIDE
INLET	(N1)	AS PER TABLE	(N5)	2 (51) FLG
OUTLET	(N2)	AS PER TABLE	(N6)	2 (51) FLG
VENT	(N4)	3/4 (19) NPT		

NOTES: 1. SUPPORTS SUPPLIED ONLY IF SPECIFIED ON ORDER.
 2. NOZZLE SIZES SHOWN ARE RECOMMENDED FOR MAXIMUM EXCHANGER LIFE.
 3. FABRICATED TO ASME CODE SECTION VIII DIVISION 1 AND LATEST ADDENDA.
 4. DRAWING IS NOT TO SCALE.
 5. ALL DIM'S ±1/8 (3) UNLESS OTHERWISE SHOWN.

DESIGN CONDITIONS				
	SHELL		TUBES	
DESIGN PRESSURE	150 PSIG	1034 KPa	150 PSIG	1034 KPa
DESIGN TEMPERATURE	375 °F	191 °C	375 °F	191 °C
MIN. DESIGN METAL TEMP.	35 °F	1.7 °C	35 °F	1.7 °C
HYDRO. TEST PRESSURE	225 PSIG	1551 KPa	300 PSIG	2068 KPa
CONTENTS	STEAM		WATER	

CUSTOMER:
 LOCATION:
 ENGINEER:
 ORDER No.:
 PROJECT/JOB:
 LOCATION:
 TAG: (QUOTE #)

TITLE: G.A. 150 LB. WS SERIES HEAT EXCHANGERS	A R M S T R O N G				NUMBER: WS-6-2P-E4-(3)	REV.
DATE: 12/01/94 BY: D.C.R.	TORONTO - CANADA TEL: (416) 755-2291	MONTREAL - CANADA TEL: (514) 421-2424	BUFFALO - N. Y. TEL: (716) 693-8813	COLCHESTER - U.K. TEL: (44) 120-657-9491		