



DIMENSIONS SHOWN AS: inches (mm)

2 - $3/4$ (19) DIA. HOLES (TYP.)

EXCHANGER SIZE	DIMENSIONS											
	A		B		C		D		(N1)		(N2)	
	inches	mm	inches	mm	inches	mm	inches	mm	inches	mm	inches	mm
WSX-62-2E2	39 1/4	997	23	584	15	381	26	660	1 1/2	38	1	25
WSX-63-2E2	51 1/4	1302	35	889	27	686	38	965	2	51	1	25
WSX-64-2E2	63 1/4	1607	47	1194	39	991	50	1270	2 1/2	64	1	25
WSX-65-2E2	75 1/4	1911	59	1499	51	1295	62	1575	2 1/2	64	1	25
WSX-66-2E2	87 1/4	2216	71	1803	63	1600	74	1880	3	76	1	25
WSX-67-2E2	99 1/4	2521	83	2108	75	1905	86	2184	3	76	1	25
WSX-68-2E2	111 1/4	2826	95	2413	87	2210	98	2489	3	76	1	25

NOZZLE SCHEDULE				
SERVICE	MARK	SHELL SIDE	MARK	TUBE SIDE
INLET	(N1)	AS PER TABLE	(N5)	2 (51) NPT
OUTLET	(N2)	AS PER TABLE	(N6)	2 (51) NPT
VENT	(N4)	3/4 (19) NPT		

NOTES:

1. SUPPORTS SUPPLIED ONLY IF SPECIFIED ON ORDER.
2. NOZZLE SIZES SHOWN ARE RECOMMENDED FOR MAXIMUM EXCHANGER LIFE.
3. FABRICATED TO ASME CODE SECTION VIII DIVISION 1 AND LATEST ADDENDA.
4. DRAWING IS NOT TO SCALE.
5. ALL DIMN'S $\pm 1/8$ (3) UNLESS OTHERWISE SHOWN.

DESIGN CONDITIONS				
	SHELL		TUBES	
DESIGN PRESSURE	150 PSIG	1034 KPa	150 PSIG	1034 KPa
DESIGN TEMPERATURE	375 °F	191 °C	375 °F	191 °C
MIN. DESIGN METAL TEMP.	35 °F	1.7 °C	35 °F	1.7 °C
HYDRO. TEST PRESSURE	225 PSIG	1551 KPa	300 PSIG	2068 KPa
CONTENTS	STEAM		WATER	

CUSTOMER:
 LOCATION:
 ENGINEER:
 ORDER No.:
 PROJECT/JOB:
 LOCATION:
 TAG: (QUOTE #)

TITLE	G.A. 150 LB. WSX SERIES HEAT EXCHANGERS				A R M S T R O N G				NUMBER	WSX-6-2P-E2- (3)	REV.			
DATE:	12 / 01 / 94	BY:	D.C.R.	TEL :	(416) 755-2291	MONTREAL - CANADA	TEL :	(514) 421-2424	BUFFALO - N. Y.	TEL :	(716) 693-8813	COLCHESTER - U.K.	TEL :	(44) 120-657-9491