



DIMENSIONS SHOWN AS: inches (mm)

EXCHANGER SIZE *-BAFFLE SPACING	DIMENSIONS											
	A		B		C		D		N1		N2	
	inches	mm	inches	mm	inches	mm	inches	mm	inches	mm	inches	mm
WX-143-4*-1	45	1143	23	584	10	254	40	1016	6	152	6	152
WX-144-4*-1	57	1448	35	889	22	559	52	1321	6	152	6	152
WX-145-4*-1	69	1753	47	1194	34	864	64	1626	6	152	6	152
WX-146-4*-1	81	2057	59	1499	46	1168	76	1930	6	152	6	152
WX-147-4*-1	93	2362	71	1803	58	1473	88	2235	6	152	6	152
WX-148-4*-1	105	2667	83	2108	70	1778	100	2540	6	152	6	152
WX-149-4*-1	117	2972	95	2413	82	2083	112	2845	6	152	6	152
WX-1410-4*-1	129	3277	107	2718	94	2388	124	3150	6	152	6	152
WX-1411-4*-1	141	3581	119	3023	106	2692	136	3454	6	152	6	152
WX-1412-4*-1	153	3886	131	3327	118	2997	148	3759	6	152	6	152
WX-1413-4*-1	165	4191	143	3632	130	3302	160	4064	6	152	6	152
WX-1414-4*-1	177	4496	155	3937	142	3607	172	4369	6	152	6	152
WX-1415-4*-1	189	4801	167	4242	154	3912	184	4674	6	152	6	152

NOZZLE SCHEDULE				
SERVICE	MARK	SHELL SIDE	MARK	TUBE SIDE
INLET	N1	AS PER TABLE	N5	4 (102) NPT
OUTLET	N2	AS PER TABLE	N6	4 (102) NPT
DRAIN	N3	1/2 (13) NPT	N7	1/2 (13) NPT
VENT	N4	3/4 (19) NPT		

NOTES: 1. SUPPORTS SUPPLIED ONLY IF SPECIFIED ON ORDER.
 2. NOZZLE SIZES SHOWN ARE RECOMMENDED FOR MAX. EXCHANGER LIFE, NO EXTERNAL FORCES APPLY.
 3. FABRICATED TO ASME CODE SECTION VIII DIVISION 1 AND LATEST ADDENDA.
 4. DRAWING IS NOT TO SCALE.
 5. ALL DIM'S $\pm 1/8$ (3) UNLESS OTHERWISE SHOWN.

DESIGN CONDITIONS				
	SHELL		TUBES	
DESIGN PRESSURE	150 PSIG	1034 KPa	125 PSIG	862 KPa
DESIGN TEMPERATURE	375 °F	191 °C	375 °F	191 °C
MIN. DESIGN METAL TEMP.	40 °F	4.4 °C	40 °F	4.4 °C
HYDRO. TEST PRESSURE	225 PSIG	1551 KPa	250 PSIG	1723 KPa
CONTENTS	WATER		WATER	

CUSTOMER: _____
 LOCATION: _____
 ENGINEER: _____
 ORDER No.: _____
 PROJECT/JOB: _____
 LOCATION: _____
 TAG: _____ (QUOTE # _____)

TITLE G.A. 150 LB. WX SERIES HEAT EXCHANGERS	A R M S T R O N G				NUMBER WX-14-4P-1(6)	REV. A ECO #9172 APRIL 16/03 J.R.
DATE: 12/01/94 BY: D.C.R.	TORONTO - CANADA TEL: (416) 755-2291	MONTREAL - CANADA TEL: (514) 421-2424	BUFFALO - N. Y. TEL: (716) 693-8813	COLCHESTER - U.K. TEL: (44) 120-657-9491		