



DIMENSIONS SHOWN AS: inches (mm)

EXCHANGER SIZE * - BAFFLE SPACING	DIMENSIONS											
	A		B		C		D		(N1)		(N2)	
	inches	mm	inches	mm	inches	mm	inches	mm	inches	mm	inches	mm
W-82-2*-3	28 5/8	727	14 1/2	368	6	152	26	660	3	76	3	76
W-83-2*-3	40 5/8	1032	26 1/2	673	18	457	38	965	3	76	3	76
W-84-2*-3	52 5/8	1337	38 1/2	978	30	762	50	1270	3	76	3	76
W-85-2*-3	64 5/8	1641	50 1/2	1283	42	1067	62	1575	3	76	3	76
W-86-2*-3	76 5/8	1946	62 1/2	1588	54	1372	74	1880	3	76	3	76
W-87-2*-3	88 5/8	2251	74 1/2	1892	66	1676	86	2184	3	76	3	76
W-88-2*-3	100 5/8	2556	86 1/2	2197	78	1981	98	2489	3	76	3	76
W-89-2*-3	112 5/8	2861	98 1/2	2502	90	2286	110	2794	3	76	3	76
W-810-2*-3	124 5/8	3165	110 1/2	2807	102	2591	122	3099	3	76	3	76
W-811-2*-3	136 5/8	3470	122 1/2	3112	114	2896	134	3404	3	76	3	76
W-812-2*-3	148 5/8	3775	134 1/2	3416	126	3200	146	3708	3	76	3	76
W-813-2*-3	160 5/8	4080	146 1/2	3721	138	3505	158	4013	3	76	3	76
W-814-2*-3	172 5/8	4385	158 1/2	4026	150	3810	170	4318	3	76	3	76

### NOZZLE SCHEDULE

SERVICE	MARK	SHELL SIDE	MARK	TUBE SIDE
INLET	(N1)	AS PER TABLE	(N5)	3 (76) NPT
OUTLET	(N2)	AS PER TABLE	(N6)	3 (76) NPT
DRAIN	(N3)	1/2 (13) NPT		
VENT	(N4)	3/4 (19) NPT		

- NOTES: 1. SUPPORTS SUPPLIED ONLY IF SPECIFIED ON ORDER.  
 2. NOZZLE SIZES SHOWN ARE RECOMMENDED FOR MAX. EXCHANGER LIFE, NO EXTERNAL FORCES APPLY.  
 3. FABRICATED TO ASME CODE SECTION VIII DIVISION 1 AND LATEST ADDENDA.  
 4. DRAWING IS NOT TO SCALE.  
 5. ALL DIMN'S ±1/8 (3) UNLESS OTHERWISE SHOWN.

### DESIGN CONDITIONS

	SHELL		TUBES	
	PSIG	KPa	PSIG	KPa
DESIGN PRESSURE	150	1034	150	1034
DESIGN TEMPERATURE	375 °F	191 °C	375 °F	191 °C
MIN. DESIGN METAL TEMP.	35 °F	1.7 °C	35 °F	1.7 °C
HYDRO. TEST PRESSURE	225	1551	225	1551
CONTENTS	WATER		WATER	

CUSTOMER:

LOCATION:

ENGINEER:

ORDER No.:

PROJECT/JOB:

LOCATION:

TAG:

(QUOTE # )

TITLE G.A. 150 LB. W SERIES  
HEAT EXCHANGERS

**A R M S T R O N G**

NUMBER

W-8-2P-3(3)

REV. A  
2001  
J.R.

DATE: 12 / 01 / 94 BY: D.C.R.

TORONTO - CANADA

TEL: (416) 755-2281

MONTREAL - CANADA

TEL: (514) 421-2424

BUFFALO - N. Y.

TEL: (716) 693-8813

COLCHESTER - U.K.

TEL: (44) 120-657-9491