



EXCHANGER SIZE * - BAFFLE SPACING	DIMENSIONS											
	A		B		C		D		N1		N2	
	inches	mm	inches	mm	inches	mm	inches	mm	inches	mm	inches	mm
WX-63-2*-4	48 3/8	1229	28	711	19	483	38	965	3	76	3	76
WX-64-2*-4	60 3/8	1534	40	1016	31	787	50	1270	3	76	3	76
WX-65-2*-4	72 3/8	1838	52	1321	43	1092	62	1575	3	76	3	76
WX-66-2*-4	84 3/8	2143	64	1626	55	1397	74	1880	3	76	3	76
WX-67-2*-4	96 3/8	2448	76	1930	67	1702	86	2184	3	76	3	76
WX-68-2*-4	108 3/8	2753	88	2235	79	2007	98	2489	3	76	3	76
WX-69-2*-4	120 3/8	3058	100	2540	91	2311	110	2794	3	76	3	76
WX-610-2*-4	132 3/8	3362	112	2845	103	2616	122	3099	3	76	3	76
WX-611-2*-4	144 3/8	3667	124	3150	115	2921	134	3404	3	76	3	76
WX-612-2*-4	156 3/8	3972	136	3454	127	3226	146	3708	3	76	3	76

NOZZLE SCHEDULE				
SERVICE	MARK	SHELL SIDE	MARK	TUBE SIDE
INLET	N1	AS PER TABLE	N5	2 (51) FLG
OUTLET	N2	AS PER TABLE	N6	2 (51) FLG
DRAIN	N3	1/2 (13) NPT		
VENT	N4	3/4 (19) NPT		

NOTES: 1. SUPPORTS SUPPLIED ONLY IF SPECIFIED ON ORDER.
 2. NOZZLE SIZES SHOWN ARE RECOMMENDED FOR MAXIMUM EXCHANGER LIFE.
 3. FABRICATED TO ASME CODE SECTION VIII DIVISION 1 AND LATEST ADDENDA.
 4. DRAWING IS NOT TO SCALE.
 5. ALL DIM'S ±1/8 (3) UNLESS OTHERWISE SHOWN.

DESIGN CONDITIONS				
	SHELL		TUBES	
DESIGN PRESSURE	150 PSIG	1034 KPa	150 PSIG	1034 KPa
DESIGN TEMPERATURE	375 °F	191 °C	375 °F	191 °C
MIN. DESIGN METAL TEMP.	35 °F	1.7 °C	35 °F	1.7 °C
HYDRO. TEST PRESSURE	225 PSIG	1551 KPa	225 PSIG	1551 KPa
CONTENTS	WATER		WATER	

CUSTOMER:
 LOCATION:
 ENGINEER:
 ORDER No.:
 PROJECT/JOB:
 LOCATION:
 TAG: (QUOTE #)

TITLE	A R M S T R O N G				NUMBER	REV.
G.A. 150 LB. WX SERIES HEAT EXCHANGERS	TORONTO - CANADA	MONTREAL - CANADA	BUFFALO - N. Y.	COLCHESTER - U.K.	WX-6-2P-4(3)	
DATE: 12/01/94 BY: D.C.R.	TEL: (416) 755-2291	TEL: (514) 421-2424	TEL: (716) 693-8813	TEL: (44) 120-657-9491		