



EXCHANGER SIZE *—BAFFLE SPACING	DIMENSIONS											
	A		B		C		D		N1		N2	
	inches	mm	inches	mm	inches	mm	inches	mm	inches	mm	inches	mm
WX-62-4*-3	28 3/4	730	16	406	7	178	27	686	2	51	2	51
WX-63-4*-3	40 3/4	1035	28	711	19	483	39	991	2	51	2	51
WX-64-4*-3	52 3/4	1340	40	1016	31	787	51	1295	2	51	2	51
WX-65-4*-3	64 3/4	1645	52	1321	43	1092	63	1600	2	51	2	51
WX-66-4*-3	76 3/4	1950	64	1626	55	1397	75	1905	2	51	2	51
WX-67-4*-3	88 3/4	2254	76	1930	67	1702	87	2210	2	51	2	51
WX-68-4*-3	100 3/4	2559	88	2235	79	2007	99	2515	2	51	2	51
WX-69-4*-3	112 3/4	2864	100	2540	91	2311	111	2819	2	51	2	51
WX-610-4*-3	124 3/4	3169	112	2845	103	2616	123	3124	2	51	2	51
WX-611-4*-3	136 3/4	3474	124	3150	115	2921	135	3429	2	51	2	51
WX-612-4*-3	148 3/4	3778	136	3454	127	3226	147	3734	2	51	2	51

NOZZLE SCHEDULE				
SERVICE	MARK	SHELL SIDE	MARK	TUBE SIDE
INLET	N1	AS PER TABLE	N5	1 1/2 (38) NPT
OUTLET	N2	AS PER TABLE	N6	1 1/2 (38) NPT
DRAIN	N3	1/2 (13) NPT	N7	1/2 (13) NPT
VENT	N4	3/4 (19) NPT		

NOTES: 1. SUPPORTS SUPPLIED ONLY IF SPECIFIED ON ORDER.
 2. NOZZLE SIZES SHOWN ARE RECOMMENDED FOR MAXIMUM EXCHANGER LIFE.
 3. FABRICATED TO ASME CODE SECTION VIII DIVISION 1 AND LATEST ADDENDA.
 4. DRAWING IS NOT TO SCALE.
 5. ALL DIM'S ±1/8 (3) UNLESS OTHERWISE SHOWN.

DESIGN CONDITIONS				
	SHELL		TUBES	
DESIGN PRESSURE	150 PSIG	1034 KPa	150 PSIG	1034 KPa
DESIGN TEMPERATURE	375 °F	191 °C	375 °F	191 °C
MIN. DESIGN METAL TEMP.	35 °F	1.7 °C	35 °F	1.7 °C
HYDRO. TEST PRESSURE	225 PSIG	1551 KPa	225 PSIG	1551 KPa
CONTENTS	WATER		WATER	

CUSTOMER:
 LOCATION:
 ENGINEER:
 ORDER No.:
 PROJECT/JOB:
 LOCATION:
 TAG: (QUOTE #)

TITLE	G.A. 150 LB. WX SERIES HEAT EXCHANGERS				A R M S T R O N G				NUMBER	REV.
DATE:	12 / 01 / 94	BY:	D.C.R.	TORONTO - CANADA	MONTREAL - CANADA	BUFFALO - N. Y.	COLCHESTER - U.K.	WX-6-4P-3(2)		
				TEL : (416) 755-2291	TEL : (514) 421-2424	TEL: (716) 693-8813	TEL: (44) 120-657-9491			