

SYSTEM ENVELOPE FLUID MANAGEMENT STATION | SEFMS-XX-TRXX-XXX.0 | SUBMITTAL

File No: 91.203
 Date: JANUARY 19, 2026
 Supersedes: NEW
 Date: NEW

Job: _____ Representative: _____

Order No: _____ Date: _____

Engineer: _____ Submitted by: _____ Date: _____

Contractor: _____ Approved by: _____ Date: _____

PUMP DESIGN DATA

No. of modules: 3 Tag: _____

Total system design flow: _____ USgpm(L/s)

Head: _____ ft(m)

Capacity split per Tango Head: 16.67%

Flow per pump head: _____ USgpm(L/s)

Parallel flow: _____ USgpm(L/s)

Liquid: _____ Viscosity: _____

Temperature: _____ °F (°C) Specific gravity: _____

Suction: _____ Discharge: _____

Min Flow Redundancy: _____

System type:

- Chilled Water Primary Loop
- Chilled Water Secondary Loop
- Heating System
- Heat Pump System

UL STD 778 & CSA STD C22.2 NO.108 certified

Test report is supplied with each pump

MATERIALS OF CONSTRUCTION

- ANSI 125**

CONSTRUCTION: SF

E-coated cast iron, 316 stainless steel fitted

MECHANICAL SEAL DESIGN DATA

See file no. 43.50 for standard mechanical seal details as indicated below

Armstrong seal reference number

- c1 (a) Others: _____

DEPMH MOTOR AND CONTROL DATA

HP: _____

Motor enclosure: TEFC

Volts: _____

Phase: 3

Efficiency: IE5

Protocol (standard): BACnet™ MS/TP BACnet™ TCP/IP
 Modbus RTU

Enclosure: Indoor - UL TYPE 12

EMI/RFI control: Integrated filter designed to meet
 EN61800-3

Harmonic suppression: Dual dc-link reactors (Equivalent: 5% AC line reactor) Supporting IEEE 519-1992 requirements**

System Flow Turndown: _____

Control: SE-F10.1

Cooling: Fan-cooled through back channel

Ambient temperature: -10°C to +45°C up to 1000 meters above sea level (+14°F to +113°F, 3300 ft)

Analog I/O: Two current or voltage inputs, one speed output

Digital I/O: Two inputs, two outputs

Pulse inputs: Two programmable

Relay outputs: Two programmable

Communication port: 1-RS485

** The IVs drive is a low harmonic drive via built-in dc line reactors. This does not guarantee performance to any system wide harmonic specification or the costs to meet a system wide specification. If supplied with the system electrical details, Armstrong will run a computer simulation of the system wide harmonics. If system harmonic levels are exceeded Armstrong can also recommend additional harmonic mitigation and the costs for such mitigation.

FLOW READOUT ACCURACY

The Design Envelope model selected will provide flow reading on the controls local keypad & digitally for the BMS. The model readout will be factory tested to ensure ±5% accuracy.

OPTIONS**SENSORLESS BUNDLE (STANDARD)**

Operation of pump without a remote sensor.

Includes:

- Sensorless control
- Flow readout
- Constant flow
- Constant pressure

Minimum system pressure to be maintained

ft (m)

* If minimum maintained system pressure is not known: Default to 40% of design head

□ PARALLEL SENSORLESS

Operation of multiple pumps without a remote sensor

Minimum system pressure to be maintained

ft (m)

* If minimum maintained system pressure is not known: Default to 40% of design head

□ ENERGY PERFORMANCE BUNDLE

Provides energy savings on oversized systems by adjusting pump parameters to on-site conditions.

Includes:

- **Auto-flow balancing** - Automatically determines control curve between design flow at on-site system head, and minimum (zero-head) flow for energy savings
- **Maximum flow control** - Limits flow rate to pre-set maximum for potential energy savings

Maximum flow rate _____ gpm (L/s)

*Only available if sensorless bundle is enabled

*Available in single pump operation only

□ PROTECTION BUNDLE

Protects other flow sensitive equipment by setting limits of pump operation. Includes:

- **Minimum flow control** - Attempts to maintain flow rate to pre-set minimum to protect equipment in system
- **Bypass valve control** - Actuates a bypass valve to protect flow sensitive equipment if pre-set minimum flow rate is reached

Minimum flow rate _____ gpm (L/s)

*Only available if sensorless bundle is enabled

□ DUAL SEASON SETUP

Pre-sets heating and cooling parameters for pumps in 2-pipe systems

Cooling

Duty point _____ gpm (L/s) at _____ ft (m)

Minimum system pressure to be maintained _____ ft (m)

Heating

Duty point _____ gpm (L/s) at _____ ft (m)

Minimum system pressure to be maintained _____ ft (m)

*Available in single pump operation only

OPTIONAL SERVICES**ON-SITE PUMP COMMISSIONING****ENVELOPE CORE**

Online service for sustained pump performance and enhanced reliability.

Available in 3 or 5 year terms



* Requires an internet connection to be provided by building


* Includes an extended warranty for parts and labour (wearable parts excluded)

*Only available if sensorless bundle is enabled

DIMENSION DATA - TRIPLEX

PUMP MODEL	NOTE	SEFMS MODEL (NEMA)	DIMENSIONS in inches(mm)										WEIGHT in lbs (kg)		SYSTEM CONNECTION	
			A	B	C	D	E	F	G	H	J	DRY	WET	INLET	OUTLET	
4322-0205-010	c/w SE-F10.1	SEFMS-08-TR04-060.0	92.90 (2360)	65.38 (1661)	82.00 (2083)	62.50 (1588)	50.00 (1270)	21.20 (538)	144.23 (3663)	47.00 (1194)	57.47 (1460)	3583 (1625.2)	4023 (1824.8)	8"	8"	
4322-2505-007.5	c/w SE-F10.1	SEFMS-08-TR06-045.0	92.75 (2356)	65.38 (1661)	82.00 (2083)	55.90 (1420)	48.50 (1232)	21.20 (538)	144.50 (3670)	47.00 (1194)	57.47 (1460)	3581 (1624.3)	4016 (1821.4)	8"	8"	
4332-0406B-015	c/w SE-F10.1	SEFMS-12-TR08-090.0	116.95 (2971)	69.15 (1756)	106.00 (2692)	68.08 (1729)	50.20 (1275)	28.00 (711)	178.62 (4537)	49.00 (1245)	59.50 (1511)	5172 (2346.0)	6947 (3151.1)	12"	12"	
4332-0406C-025	c/w SE-F10.1	SEFMS-14-TR12-150.0	116.95 (2971)	72.90 (1852)	106.00 (2692)	74.19 (1884)	53.32 (1354)	23.15 (588)	196.09 (4981)	49.00 (1245)	59.50 (1511)	6500 (2948.4)	8900 (4037.0)	14"	14"	
4332-0407-040*	c/w SE-F10.1	SEFMS-14-TR18-240.0	116.95 (2970)	72.90 (1852)	106.00 (2692)	74.19 (1884)	57.35 (1457)	23.14 (588)	196.09 (4981)	49.00 (1245)	59.50 (1511)	6565 (2977.8)	8965 (4066.5)	14"	14"	





NOTE: The pump weight is not included in the listed weights.