



EXCHANGER SIZE	DIMENSIONS								NOZZLE SCHEDULE			
	"A"		"B"		"C"		"D"		N1 INLET	8" FLG (203)	N2 OUTLET	8" FLG (203)
	Inches	mm	Inches	mm	Inches	mm	Inches	mm				
THWX-1824-2-2	41 -7/8	1064	23-1/2	597	27	686	11-3/4	298	N3 DRAIN	1/2" NPT	(13)	
THWX-1830-2-2	47 -7/8	1216	29-1/2	749	33	838	17-3/4	451	COLLAR ASSEMBLY			
THWX-1836-2-2	53 -7/8	1368	35-1/2	902	39	991	23-3/4	603		STANDARD	OVS. FOR STONE LINING	
THWX-1842-2-2	59 -7/8	1521	41-1/2	1054	45	1143	29-3/4	756	"E"	18" (457)	20" (508)	
THWX-1848-2-2	65 -7/8	1673	47-1/2	1207	51	1295	35-3/4	908	"F"	12-1/2" (318)	14" (356)	
THWX-1854-2-2	71 -7/8	1826	53-1/2	1359	57	1448	41-3/4	1060	DESIGN CONDITIONS			
THWX-1860-2-2	77 -7/8	1978	59-1/2	1511	63	1600	47-3/4	1213		TUBES		
THWX-1866-2-2	83 -7/8	2130	65-1/2	1664	69	1753	53-3/4	1365	DESIGN PRESSURE	150 PSIG	1034 KPa	
THWX-1872-2-2	89 -7/8	2283	71-1/2	1816	75	1905	59-3/4	1518	DESIGN TEMPERATURE	375 F	191 C	
THWX-1878-2-2	95 -7/8	2435	77-1/2	1969	81	2057	65-3/4	1670	M.D.M.T.	40 F	4.4 C	
THWX-1884-2-2	101 -7/8	2588	83-1/2	2121	87	2210	71-3/4	1822	HYD. TEST PRESSURE	300 PSIG	2068 KPa	
THWX-1890-2-2	107 -7/8	2740	89-1/2	2274	93	2362	77-3/4	1975	NOTES:			
THWX-1896-2-2	113 -7/8	2892	95-1/2	2426	99	2515	83-3/4	2127	1. COLLAR ASSEMBLY SUPPLIED SEPARATELY.			
THWX-18102-2-2	119 -7/8	3045	101-1/2	2578	105	2667	89-3/4	2280	2. FABRICATED TO ASME CODE SECTION VIII DIVISION 1 AND LATEST ADDENDA.			
THWX-18108-2-2	125 -7/8	3197	107-1/2	2731	111	2819	95-3/4	2432	3. DRAWING IS NOT TO SCALE.			
THWX-18114-2-2	131 -7/8	3350	113-1/2	2883	117	2972	101-3/4	2584	4. ALL DIM'S 1/8 (3) UNLESS OTHERWISE SHOWN.			
THWX-18120-2-2	137 -7/8	3502	119-1/2	3035	123	3124	107-3/4	2737	5. DIMENSIONS SHOWN AS: In.(mm)			
THWX-18126-2-2	143 -7/8	3654	125-1/2	3188	129	3277	113-3/4	2889	CUSTOMER:			
THWX-18132-2-2	149 -7/8	3807	131-1/2	3340	135	3429	119-3/4	3042	LOCATION:			
THWX-18138-2-2	155 -7/8	3959	137-1/2	3493	141	3581	125-3/4	3194	ENGINEER :			
THWX-18144-2-2	161 -7/8	4112	143-1/2	3645	147	3734	131-3/4	3346	ORDER No.:			
THWX-18150-2-2	167 -7/8	4264	149-1/2	3797	153	3886	137-3/4	3499	PROJECT/JOB:			
THWX-18156-2-2	173 -7/8	4416	155-1/2	3950	159	4039	143-3/4	3651	LOCATION:			
THWX-18162-2-2	179 -7/8	4569	161-1/2	4102	165	4191	149-3/4	3804	TAG:			
									QUOTE #			

TITLE	G.A. 150 LB. TANK HEATERS	ARMSTRONG				NUMBER	Thwx-18-2P-2	REV.	
DATE	24/05/95	BY	D.C.R	TORONTO - CANADA	MONTREAL - CANADA	BUFFALO - N. Y.	COLCHESTER - U.K.		
				TEL : (416) 755-2291	TEL : (514) 421-2424	TEL : (716) 693-8813	TEL : (44) 120-657-9491		