



EXCHANGER SIZE	DIMENSIONS											
	A		B		C		D		N1		N2	
	inches	mm	inches	mm	inches	mm	inches	mm	inches	mm	inches	mm
WS-82-2-4	36	914	13	330	4 3/4	121	26	660	2	51	1	25
WS-83-2-4	48	1219	25	635	16 3/4	425	38	965	2 1/2	64	1	25
WS-84-2-4	60	1524	37	940	28 3/4	730	50	1270	3	76	1	25

NOZZLE SCHEDULE				
SERVICE	MARK	SHELL SIDE	MARK	TUBE SIDE
INLET	(N1)	AS PER TABLE	(N5)	3 (76) FLG
OUTLET	(N2)	AS PER TABLE	(N6)	3 (76) FLG
VENT	(N4)	3/4 (19) NPT		

**NOTES:** 1. SUPPORTS SUPPLIED ONLY IF SPECIFIED ON ORDER.  
 2. NOZZLE SIZES SHOWN ARE RECOMMENDED FOR MAXIMUM EXCHANGER LIFE.  
 3. FABRICATED TO ASME CODE SECTION VIII DIVISION 1 AND LATEST ADDENDA.  
 4. DRAWING IS NOT TO SCALE.  
 5. ALL DIM'S  $\pm 1/8(3)$  UNLESS OTHERWISE SHOWN.

DESIGN CONDITIONS				
	SHELL		TUBES	
DESIGN PRESSURE	150 PSIG	1034 KP <sub>a</sub>	150 PSIG	1034 KP <sub>a</sub>
DESIGN TEMPERATURE	375 °F	191 °C	375 °F	191 °C
MIN. DESIGN METAL TEMP.	35 °F	1.7 °C	35 °F	1.7 °C
HYDRO. TEST PRESSURE	225 PSIG	1551 KP <sub>a</sub>	225 PSIG	1551 KP <sub>a</sub>
CONTENTS	STEAM		WATER	

CUSTOMER:  
 LOCATION:  
 ENGINEER:  
 ORDER No.:  
 PROJECT/JOB:  
 LOCATION:  
 TAG: (QUOTE # )

TITLE G.A. 150 LB. WS SERIES HEAT EXCHANGERS	A R M S T R O N G				NUMBER WS-8-2P-4-(3)	REV.
DATE: 12 / 01 / 94	BY: D.C.R.	TORONTO - CANADA TEL : (416) 755-2291	MONTREAL - CANADA TEL : (514) 421-2424	BUFFALO - N. Y. TEL: (716) 693-8813	COLCHESTER - U.K. TEL: (44) 120-657-9491	