



DIMENSIONS SHOWN AS: inches (mm)

EXCHANGER SIZE * - BAFFLE SPACING	DIMENSIONS											
	A		B		C		D		N1		N2	
	inches	mm	inches	mm	inches	mm	inches	mm	inches	mm	inches	mm
W-62-2*-3	28 1/8	714	16	406	7	178	25	635	2	51	2	51
W-63-2*-3	40 1/8	1019	28	711	19	483	37	940	2	51	2	51
W-64-2*-3	52 1/8	1324	40	1016	31	787	49	1245	2	51	2	51
W-65-2*-3	64 1/8	1629	52	1321	43	1092	61	1549	2	51	2	51
W-66-2*-3	76 1/8	1934	64	1626	55	1397	73	1854	2	51	2	51
W-67-2*-3	88 1/8	2238	76	1930	67	1702	85	2159	2	51	2	51
W-68-2*-3	100 1/8	2543	88	2235	79	2007	97	2464	2	51	2	51
W-69-2*-3	112 1/8	2848	100	2540	91	2311	109	2769	2	51	2	51
W-610-2*-3	124 1/8	3153	112	2845	103	2616	121	3073	2	51	2	51
W-611-2*-3	136 1/8	3458	124	3150	115	2921	133	3378	2	51	2	51
W-612-2*-3	148 1/8	3762	136	3454	127	3226	145	3683	2	51	2	51

**NOZZLE SCHEDULE**

SERVICE	MARK	SHELL SIDE	MARK	TUBE SIDE
INLET	(N1)	AS PER TABLE	(N5)	2 (51) NPT
OUTLET	(N2)	AS PER TABLE	(N6)	2 (51) NPT
DRAIN	(N3)	1/2 (13) NPT		
VENT	(N4)	3/4 (19) NPT		

- NOTES:**
1. SUPPORTS SUPPLIED ONLY IF SPECIFIED ON ORDER.
  2. NOZZLE SIZES SHOWN ARE RECOMMENDED FOR MAXIMUM EXCHANGER LIFE.
  3. FABRICATED TO ASME CODE SECTION VIII DIVISION 1 AND LATEST ADDENDA.
  4. DRAWING IS NOT TO SCALE.
  5. ALL DIMN'S ±1/8 (3) UNLESS OTHERWISE SHOWN.

**DESIGN CONDITIONS**

	SHELL		TUBES	
	PSIG	KPa	PSIG	KPa
DESIGN PRESSURE	150	1034	150	1034
DESIGN TEMPERATURE	375 °F	191 °C	375 °F	191 °C
MIN. DESIGN METAL TEMP.	35 °F	1.7 °C	35 °F	1.7 °C
HYDRO. TEST PRESSURE	225	1551	225	1551
CONTENTS	WATER		WATER	

CUSTOMER:

LOCATION:

ENGINEER:

ORDER No.:

PROJECT/JOB:

LOCATION:

TAG:

(QUOTE # )

TITLE	G.A. 150 LB. W SERIES HEAT EXCHANGERS				A R M S T R O N G				NUMBER	REV.			
DATE:	12 / 01 / 94	BY:	D.C.R.	TEL :	(416) 755-2291	TEL :	(514) 421-2424	TEL :	(716) 693-8813	TEL :	(44) 120-657-9491	W-6-2P-3-(2)	