



DIMENSIONS SHOWN AS: inches (mm)

EXCHANGER SIZE	DIMENSIONS								NOZZLE SCHEDULE		
	"A"		"B"		"C"		"D"		N1	INLET	
	Inches	mm	Inches	mm	Inches	mm	Inches	mm	4" FLG	(102)	
THWX-1236-2-2	48 -5/8	1235	35-3/4	908	38	965	24-5/16	618	N2	OUTLET 4" FLG (102)	
THWX-1242-2-2	54 -5/8	1387	41-3/4	1060	44	1118	30-5/16	770	N3	DRAIN 1/2" NPT (13)	
THWX-1248-2-2	60 -5/8	1540	47-3/4	1213	50	1270	36-5/16	922	COLLAR ASSEMBLY		
THWX-1254-2-2	66 -5/8	1692	53-3/4	1365	56	1422	42-5/16	1075	STANDARD		OVS. FOR STONE LINING
THWX-1260-2-2	72 -5/8	1845	59-3/4	1518	62	1575	48-5/16	1227	"E"	12-3/4 (324)	14 (356)
THWX-1266-2-2	78 -5/8	1997	65-3/4	1670	68	1727	54-5/16	1380	"F"	10 (254)	10-1/2 (267)
THWX-1272-2-2	84 -5/8	2149	71-3/4	1822	74	1880	60-5/16	1532	DESIGN CONDITIONS		
THWX-1278-2-2	90 -5/8	2302	77-3/4	1975	80	2032	66-5/16	1684	TUBES		
THWX-1284-2-2	96 -5/8	2454	83-3/4	2127	86	2184	72-5/16	1837	DESIGN PRESSURE	150 PSIG	1034 KPa
THWX-1290-2-2	102 -5/8	2607	89-3/4	2280	92	2337	78-5/16	1989	DESIGN TEMPERATURE	300 F	149 C
THWX-1296-2-2	108 -5/8	2759	95-3/4	2432	98	2489	84-5/16	2142	M.D.M.T.	35 F	1.7 C
THWX-12102-2-2	114 -5/8	2911	101-3/4	2584	104	2642	90-5/16	2294	HYD. TEST PRESSURE	300 PSIG	2068 KPa
THWX-12108-2-2	120 -5/8	3064	107-3/4	2737	110	2794	96-5/16	2446	NOTES:		
THWX-12114-2-2	126 -5/8	3216	113-3/4	2889	116	2946	102-5/16	2599	1. COLLAR ASSEMBLY SUPPLIED SEPARATELY.		
THWX-12120-2-2	132 -5/8	3369	119-3/4	3042	122	3099	108-5/16	2751	2. FABRICATED TO ASME CODE SECTION VIII DIVISION 1 AND LATEST ADDENDA.		
THWX-12126-2-2	138 -5/8	3521	125-3/4	3194	128	3251	114-5/16	2904	3. DRAWING IS NOT TO SCALE.		
THWX-12132-2-2	144 -5/8	3673	131-3/4	3346	134	3404	120-5/16	3056	4. ALL DIM'S 1/8 (3) UNLESS OTHERWISE SHOWN.		
THWX-12138-2-2	150 -5/8	3826	137-3/4	3499	140	3556	126-5/16	3208	5. DIMENSIONS SHOWN AS: in.(mm)		
THWX-12144-2-2	156 -5/8	3978	143-3/4	3651	146	3708	132-5/16	3361	CUSTOMER:		
THWX-12150-2-2	162 -5/8	4131	149-3/4	3804	152	3861	138-5/16	3513	LOCATION:		
THWX-12156-2-2	168 -5/8	4283	155-3/4	3956	158	4013	144-5/16	3666	ENGINEER :		
THWX-12162-2-2	174 -5/8	4435	161-3/4	4108	164	4166	150-5/16	3818	ORDER No.:		
									PROJECT/JOB:		
									LOCATION:		
									TAG:		
									QUOTE #		

TITLE
G.A. 150 LB. TANK HEATERS
DATE : 24/05/95 BY : D.C.R

ARMSTRONG
TORONTO - CANADA MONTREAL - CANADA BUFFALO - N. Y. COLCHESTER - U.K.
TEL : (416) 755-2291 TEL : (514) 421-2424 TEL : (716) 693-8813 TEL : (44) 120-657-9491

NUMBER
Thwx-12-2P-2
REV.