



EXCHANGER SIZE	DIMENSIONS								NOZZLE SCHEDULE		
	"A"		"B"		"C"		"D"		(N1) INLET	8" FLG (203)	
	Inches	mm	Inches	mm	Inches	mm	Inches	mm	(N2) OUTLET	8" FLG (203)	
THWX-2030-2-2	48 -3/8	1229	29-1/2	749	33	838	13-3/8	340	(N3) DRAIN	1/2" NPT (13)	
THWX-2036-2-2	54 -3/8	1381	35-1/2	902	39	991	19-3/8	492	COLLAR ASSEMBLY		
THWX-2042-2-2	60 -3/8	1534	41-1/2	1054	45	1143	25-3/8	645		STANDARD	OVS. FOR STONE LINING
THWX-2048-2-2	66 -3/8	1686	47-1/2	1207	51	1295	31-3/8	797	"E"	20" (508)	22" (559)
THWX-2054-2-2	72 -3/8	1838	53-1/2	1359	57	1448	37-3/8	949	"F"	14" (254)	16-1/2" (419)
THWX-2060-2-2	78 -3/8	1991	59-1/2	1511	63	1600	43-3/8	1102	DESIGN CONDITIONS		
THWX-2066-2-2	84 -3/8	2143	65-1/2	1664	69	1753	49-3/8	1254	TUBES		
THWX-2072-2-2	90 -3/8	2296	71-1/2	1816	75	1905	55-3/8	1407	DESIGN PRESSURE	150 PSIG	1034 KPa
THWX-2078-2-2	96 -3/8	2448	77-1/2	1969	81	2057	61-3/8	1559	DESIGN TEMPERATURE	375 F	191 C
THWX-2084-2-2	102 -3/8	2600	83-1/2	2121	87	2210	67-3/8	1711	M.D.M.T.	40 F	4.4 C
THWX-2090-2-2	108 -3/8	2753	89-1/2	2274	93	2362	73-3/8	1864	HYDRO TEST PRESSURE	300 PSIG	2068 KPa
THWX-2096-2-2	114 -3/8	2905	95-1/2	2426	99	2515	79-3/8	2016	NOTES:		
THWX-20102-2-2	120 -3/8	3058	101-1/2	2578	105	2667	85-3/8	2169	1. COLLAR ASSEMBLY SUPPLIED SEPARATELY.		
THWX-20108-2-2	126 -3/8	3210	107-1/2	2731	111	2819	91-3/8	2321	2. FABRICATED TO ASME CODE SECTION VIII DIVISION 1 AND LATEST ADDENDA.		
THWX-20114-2-2	132 -3/8	3362	113-1/2	2883	117	2972	97-3/8	2473	3. DRAWING IS NOT TO SCALE.		
THWX-20120-2-2	138 -3/8	3515	119-1/2	3035	123	3124	103-3/8	2626	4. ALL DIM'S 1/8 (3) UNLESS OTHERWISE SHOWN.		
THWX-20126-2-2	144 -3/8	3667	125-1/2	3188	129	3277	109-3/8	2778	5. DIMENSIONS SHOWN AS: In.(mm)		
THWX-20132-2-2	150 -3/8	3820	131-1/2	3340	135	3429	115-3/8	2931	CUSTOMER:		
THWX-20138-2-2	156 -3/8	3972	137-1/2	3493	141	3581	121-3/8	3083	LOCATION:		
THWX-20144-2-2	162 -3/8	4124	143-1/2	3645	147	3734	127-3/8	3235	ENGINEER :		
THWX-20150-2-2	168 -3/8	4277	149-1/2	3797	153	3886	133-3/8	3388	ORDER No.:		
THWX-20156-2-2	174 -3/8	4429	155-1/2	3950	159	4039	139-3/8	3540	PROJECT/JOB:		
THWX-20162-2-2	180 -3/8	4582	161-1/2	4102	165	4191	145-3/8	3693	LOCATION:		
									TAG:		
									QUOTE #		

TITLE	G.A. 150 LB. TANK HEATERS	ARMSTRONG				NUMBER	Thwx-20-2P-2	REV.
DATE	24/05/95	BY	D.C.R	TORONTO - CANADA	MONTREAL - CANADA	BUFFALO - N. Y.	COLCHESTER - U.K.	
				TEL: (416) 755-2291	TEL: (514) 421-2424	TEL: (716) 693-8813	TEL: (44) 120-657-9491	