

360 LIFECYCLE SERVICE AND SUPPORT

AUTOMATION & OPTIMIZATION

PACKAGED SYSTEMS



BOOSTERS

CIRCULATORS

FIRE SAFETY

REPLACEMENT PARTS

Your guide to the complete line of Armstrong performance solutions

FILE NO: 9.09 DATE: MARCH 2022 SUPERSEDES: 9.09 DATE: OCTOBER 2018



BUILDING LIFECYCLE PERFORMANCE SOLUTIONS

FROM THE SMART BUILDING PERFORMANCE EXPERTS



 \bigcirc

building doesn't move much, but it has to work.

Every day. For decades. A building has to last. It has to withstand the elements and the ravages of time. It has to endure.

Armstrong provides solutions to help buildings perform and endure.



Just like a building that has to endure, our earth, our planet, also has to endure. Armstrong products and solutions help buildings and building owners minimize the environmental impact of their operations.

Armstrong Fluid Technology is known the world over as an innovator for designing, engineering and manufacturing intelligent fluid flow equipment, control solutions and digital technologies.

In the application of technology to mechanical systems for buildings, Armstrong is a change agent and a thought leader, taking mechanical systems to entirely new levels of operating efficiency.

Drawing on our experience and our history of service, Armstrong is able to serve a wide range of industries and contribute to mechanical systems in a diverse set of building types, supporting air conditioning, heating, commercial cooling, domestic water and fire safety systems.

5	DESIGN ENVELOPE TECHNOLOGY	13	PUMP
A N	Armstrong's innovative Design Envelope technology combines highest operating efficiency with lowest installed cost and lowest operating cost for your application.		Our experi variable sp leading ou
7	ACTIVE PERFORMANCE MANAGEMENT	19	BOOS
	From a single pump to an entire plant, Armstrong can help your system learn, predict and optimize performance at every level to make your project a success.		The most of equipment fill, no-flow
9	360 SERVICE & SUPPORT	20	CIRCU
	Armstrong provides complete solution support to help you get the best possible performance from your mechanical systems, at every phase in the lifecycle of your building.		Wet or dry and out-of perfect ma
11	AUTOMATION & OPTIMIZATION	22	HEAT
Home Shinesecow Users I blacky for the series of the serie	We offer a range of expert services to assist you in evaluating current operational equipment and energy efficiencies, as well as delivering complete ultra-efficient chilled water plants.		High quali transfer ra and tank h
9	PACKAGED SYSTEMS	23	FIRE S
	Pre-fabricated HVAC systems for chiller and boiler plants, pumping stations, energy transfer stations, cooling tower applications, fire pump systems, and water-based process applications.		Our prover packages r application



CONTENTS

IPS

pertise in demand-based control, fluid flow, e speed, and heat transfer gives you the industryoutcomes you expect.

STERS

st efficient and safest booster and water supply ent, featuring cutting-edge capabilities such as soft low shutdown, and sensorless pressure optimization.

ULATORS

dry rotor circulators that lead in reliability, ease of repair, -of-thebox energy savings. Armstrong circulators are a match for installed based and many competing models.

FEXCHANGERS

ality and durability combined with excellent heat rates have placed Armstrong heat exchangers cheaters amongst the top in their categories.

SAFETY

ven and reliable fire safety pumps, controls, and es meet the most demanding test standards and tions, available in diesel as well as electrical versions.

See our exciting new developments in replacement part kits and accessories

DESIGN ENVELOPE





Design Envelope technology replaces mechanical components with electronics and software intelligence in order to:

Boost energy efficiency

Downsize equipment

Optimize part-load performance

As a design or building professional, this helps you achieve the lowest installed cost, lowest operating cost, and lowest environmental impact with your mechanical designs and installations. Design Envelope technology puts your projects at the sustainability forefront, in energy savings, cost savings, and carbon savings.

ENERGY SAVINGS

Savings for our clients' Design Envelope installations worldwide since 2007.

> Tonnes of CO equivalent*

kWh

electricity*

*as of April, 2021

1,813,782,505



Scan to discover more benefits of Design Envelope technology for your new or retrofit project.





LOWEST INSTALLED соѕт





CARBON EMISSIONS





The RBC

Centre has

relative to similar towers built to standard code.

○ A .002 ▲

5

DESIGN ENVELOPE

6



RBC Tower

A flexible HVAC system includes responsive HVAC controls that provide individual cooling at high efficiencies. The application draws on Toronto's Enwave deep lake water cooling system to dramatically reduce energy and operating cost.



Scan to learn more about this case study

ACTIVE PERFORMANCE MANAGEMENT

8

OPTIMIZED EFFICIENCY AND PERFORMANCE

7

ACTIVE PERFORMANCE MANAGEMENT[™]


LEARNS PREDICTS OPTIMIZES

With Active Performance Management at the plant level, you can save up to

40%

annual energy savings

Active Performance Management is a systems management approach that optimizes HVAC systems at any stage of a building's life-cycle by continuously learning from a broad network of installations and responding to changing HVAC requirements. The combination of smart commissioning with real-time alerts and system transparency addresses performance drift and maintains occupant comfort.





FLOW INFORMS

The rate of fluid flow in an HVAC system is crucial to understanding how the different components are operating. Without information on system flow, it's difficult to diagnose and optimize performance. With accurate flow information, the picture changes entirely. Armstrong can optimize each component and the overall system.



We're there for the lifecycle of plant and equipment operations



Rapid response attention

MATCHED TO YOUR NEEDS.

24/7 GLOBAL RAPID RESPONSE





360 SERVICES

with modular, packaged systems.

COMMISSION

Armstrong offers a reduced timeframe, and energy savings from day one.

Speed-to-market and

quality are assured

Our service plans ensure maximum equipment uptime through realtime performance management, informed system optimization and expert support for your building assets.


Pump Manager[™]

Real-time operating insights and early diagnostic warnings

Full transparency in energy savings and carbon footprint reduction

Reduce pump maintenance cost by up to 50% with predictive maintenance

Itimate system performance requires seamless integration of mechanical U equipment, sensing and controls — with solid technical and logistics support. Armstrong HVAC control systems enable you to meet operating budgets, project schedules and environmental goals with a single point of supplier accountability.



upgrading system assets.

searching for

their results.

ways to improve

DESIGN ENVELOPE EVERCOOL™

· Air-cooled or water-cooled chilled water system automation for data centers





With the maximum share of work completed in-factory, all that is needed for the completion of the project is to have the packaged plant connected on-site. Armstrong's packaged plants feature insulated structural design, matching or exceeding building code requirements



PACKAGED SYSTEMS

- rmstrong packaged systems Reduced risk to project schedule
 - Reduced risk of scope omissions and cost impacts
 - Conformance to construction schedule
 - Single point of supplier accountability
 - Expert design for optimal performance





COMMERCIAL



FEATURE: DESIGN ENVELOPE INTELLIGENT FLUID MANAGEMENT SYSTEM

 Integrates pump and control technology into a single pumping solution yielding: + compact footprint

+ energy efficiency

+ rapid installation

 Catalogue-based pre-engineered solutions or custom-designed to specification





rmstrong pumps have been synonymous with superior design, Α reliability, maintainability, and operating efficiency. Design Envelope pumps deliver the lowest installed and lowest operating costs — resulting in the shortest payback periods compared to any other pumping equipment available in the market today.

MODELS AVAILABLE FOR PLUMBING AND POTABLE WATER APPLICATIONS

NEW DEPM PUMPS FOR OUTDOOR **OPERATIONS AND HIGHER** HORSEPOWER Controls enclosure rated for UL Type 4x

Equipped with overhead weather shield to prevent pump from icing and overheating



DESIGN ENVELOPE 4372 TANGO PUMPS



VERTICAL IN-LINE CLOSE-COUPLED

Base mounted endsuction horizontal pumping unit with

integrated intellige controls for easier installation • 25 to 4500 USgpm

flow; 10 to 400 ft head • Power: 1 hp to 125 hp

• Temperature: 300°F

DESIGN ENVELOPE 4200H

• Size: 1.5" to 8"



 Pipe-mounted twopump unit with intearated intelligent controls and duty/ standby or parallel pumping operation • Up to 1250 USgpm

Pipe-mounted

two-pump unit with

controls for space-

saving installation

Up to 900 USgpm

integrated intelligent

flow; up to 160 ft head

Temperature: 300°F

• Power: 1 hp to 10 hp

• Size: 1½" to 3"

DESIGN ENVELOPE

4322 TANGO PUMPS

flow; up to 250 ft head Temperature: 250°F

- Power: 1 hp to 75 hp
- Size: 3" to 8"

DESIGN ENVELOPE 4302 DUALARM PUMPS

• Pipe-mounted UL 778 pumping unit with integrated intelligent controls for spacesaving installation and superior energy performance • 25 to 25,000 USgpm

SIGN

flow; 10 to 300 ft head • Temperature: 300°F

- Power: 1 hp to 1250 hp
- Size: 1½" to 20"

DESIGN ENVELOPE **4300 PUMPS**





Pipe-mounted twopump unit with intearated intelligent controls and duty/ standby or parallelpumping operation • Up to 1000 USgpm flow; up to 140 ft head Temperature: 250°F

• Power: 1 hp to 7½ hp • Size: 3" to 8"

DESIGN ENVELOPE 4382 DUALARM PUMPS

• Pipe-mounted pump unit with integrated intelligent controls for space-saving installation and superior energy performance Up to 1000 USapm flow; up to 140 ft head

Temperature: 250°F

• Power: 1 hp to 10 hp • Size: 1½" to 6"

DESIGN ENVELOPE **4380 PUMPS**





 \mathcal{Q} FACILITY TYPE LOCATION Commercial Solihull, office Birmingham

КЛ SIZE Three-storey building

下 フ



14

.

HORIZONTAL

A new 15 hp to 50 hp range of Design Envelope Permanent Magnet pumps deliver 20% lowe operating costs than pumps with standard induction motors



- Motor-mounted pum unit with integrated intelligent controls for space-saving installation
- Up to 1000 USgpm flow; up to 125 ft head
- Power: 1 hp to 7.5 hp
- Temperature: 250°F
- Size: 1.5" to 6"

DESIGN ENVELOPE 4280

ANNUAL

ENERGY SAVINGS

VERIFIED 32%

ANNUAL ENERGY COST

£16,076 £10,866

AFTER

AVERAGE

<u></u>

BEFORE

AVERAGE

CASE STUDY





rmstrong completed a project in the United Kingdom, retrofitting a building belonging to National Grid.

The retrofit included new pump sets that reduced energy consumption by 32%, saving over 5,000 GBP annually.

SOLUTION









flow; up to 500 ft head Temperature: 300°F • Power: 1 hp to 1250 hp

• Size: 1½" to 20"

4300 VERTICAL **IN-LINE PUMPS**

VERTICAL IN-LINE SPLIT-COUPLED



 Temperature: 250°F • Power: 0.25 hp to 10 hp

VERTICAL IN-LINE CLOSE-COUPLED

• Size: 1" to 6"

4280 SINGLE-PHASE DEPM PUMPS



VERTICAL IN-LINE SPLIT-COUPLED



• Up to 1250 USgpm flow; up to 400 ft head

• Power: 1 hp to 100 hp

 Temperature: 121°F • Size: 2" to 6"

4312 VERTICAL IN-LINE TWIN PUMPS





CASE STUDY



Bernardin Manor

ernardin Manor is an B assisted living facility in Chicago. Armstrong proposed to upgrade existing constant speed pumps with new Design Envelope Tango pumps.

The three new, properly sized pumps are operating much more efficiently than the original pumps. **Energy savings from the pump** retrofit will be over \$4,000 per year.







CASE STUDY

4392 VERTICAL

IN-LINE TWIN PUMPS



Texas Christian University

ith enrollment of over W 10,000 students per year, athletics is a key focus for тси university, with the Horned Frogs competing in the Big 12 conference of the ncaas.

Armstrong approached TCU with a proposal to upgrade three constant-speed pumps in the **Recreation Center. As a result of** the retrofit project, TCU is saving over \$7,500 per year.







BOOSTERS

D esign Envelope Boosters combine advanced controls with NEMA Premium efficiency induction motors (IE3) and new DEPM (IE5) motors that surpass NEMA Super-premium efficiency. These designs optimize system-wide pressure boosting efficiency and reduce energy costs. Intelligent pump staging, automatic set-point adjustment and integrated variable frequency drives provide even greater savings. All Armstrong boosters are available in lead-free versions that meet the most stringent industry standards for potable water. he Armstrong Design Envelope Compass circulator embeds the latest motor and control technologies, providing you with the ultimate in flexibility, operating comfort, and energy efficiency. Our broad offering of wet-rotor and dry-rotor designs help you respond to any hydronic situation with ease and confidence.

 Excellent all-purpose solution for applications requiring higher flowrates and boost pressures. Multiple pump configurations ensure design flexibility and ease of install and commissioning
 Up to 1962 USgpm flow; up to 320 psi

DESIGN ENVELOPE 6800 VERTICAL MULTISTAGE BOOSTERS

• Power: Up to 250 hp

The perfect solution for small and mediumsized applications. Compact design has the smallest footprint in the industry
Up to 500 USgpm flow; up to 100 psi
Power: Up to 40 hp

DESIGN ENVELOPE 6900 VERTICAL BOOSTERS



Footprint of

MINIMAL

FOOTPRINT

OF 25%

competing models

SPACE SAVINGS

 Designed to replace existing fixed speed circulators, with popular flange-toflange dimensions. A universal replacement for all circulators

in its capacity range
Cast iron and stainless
steel volutes

Up to 20 USgpm flow; up to 20 ft head
Power: 5W to 45W

DESIGN ENVELOPE COMPASS H CIRCULATOR

- Circulates water or ethylene-glycol solutions in closed hydronic or solar heating systems. Available in two volute materials for residential, small industrial, and commercial applications
- Up to 64 USgpm flow; up to 42 ft head
 Power: 33W to 218W

ASTRO 2 CIRCULATORS

 Designed to replace existing fixed speed circulators, with popular flange-to-flange dimensions.
 A universal replacement for all circulators in its capacity range

Cast iron and stainless
 steel volutes

Up to 140 USgpm flow; up to 40 ft head
Power: ¹/₄-¹/₂ hp

DESIGN ENVELOPE COMPASS R CIRCULATOR



WET ROTOR DESIGN

DRY ROTOR DESIGN




 The leading solution in the industry. DEPM motors with Design Envelope technology maximize efficiency, reduce noise and ensure reliability
 Up to 580 USgpm flow; up to 250 psi

• Power: up to 50 hp

DESIGN ENVELOPE DEPM 6800G VERTICAL MULTISTAGE BOOSTERS

> DEPM motors provide a clear efficiency advantage across the operating range and the difference in efficiency levels is even greater at lower speeds.



* Including Permanent Magnet

Design Envelope 6800*

Competing models 77"× 48"

Reduced maintenance requirements Longer uninterrupted operating times

Smaller size and reduced weight

Ultra-quiet operation

Larger range of operating speeds

Maximum design and installation flexibility

CIRCULATORS

MODELS AVAILABLE FOR PLUMBING AND POTABLE WATER APPLICATIONS

DRY ROTOR DESIGN

point efficiencies
Up to 140 USgpm flow; up to 60 ft head

Draws on advanced

motor technology and

efficient hydraulic de-

sign to achieve excel-

lent wire-to-water duty

- Temperature: 110°F
- Power: ¼ hp to ½ hp
- Size: 3/4" to 3"

E.2 CIRCULATORS

- For commercial systems that require higher flow and pressure. Offers the flexibility of customizing the flow curve to specific application requirements
- Up to 250 USgpm flow; up to 55 ft head
- Temperature: 107°F
- Power: ¼ hp to 3 hp
- Size: 3⁄4" to 3"


1050/1060, 3-PIECE CIRCULATORS

- For commercial systems that require higher flow and pressure. Offers the flexibility of customizing the flow curve to specific application requirements
- Up to 250 USgpm
 flow; up to 55 ft head
- Temperature: 107°F
- Power: ¼ hp to 3 hp
- Size: ¾" to 2"

S&H 3-PIECE CIRCULATORS









CASE STUDY



Crown Reality Parter Pearson Corporate

Optimized for best

water-to-water heat

enhanced performance especially in HVAC

Performance range: 150

psi standard pressure

rating. Pressure rating

upto 435 psi available

PLATE AND FRAME HEAT EXCHANGERS

transfer providing

applications

his 300,000 square foot complex in Toronto consists of two eight-storey office towers joined together by a central atrium. In 2018 the building owners asked Armstrong to upgrade the original pumps to new Design Envelope pumps.

Armstrong's new Design Envelope variable-speed pumps produce energy savings of over 80%.




HEAT EXCHANGERS


H igh quality and durability combined with excellent heat transfer rates have placed Armstrong heat exchangers and tank heaters amongst the top in their categories. In concert with other Armstrong equipment, Armstrong heat exchangers are a critical component for getting the maximum performance from your HVAC and



hen it comes to fire protection you can count on our track record of delivering reliable, durable and easy to test equipment and systems that are up to this critical task. Armstrong fire pumps and packages are constructed, tested and certified to the strictest global standards including NFPA, UL, ULC, and FM.



FIRE SAFETY



- Up to 1500 USgpm
- Max. ambient temperature: 50°F+
- Power: 20 hp to 250 hp

DESIGN ENVELOPE FIRE PUMP

FIRE PUMPS





CASE STUDY | **INOX Leisure Limited**

his leader in India's cinema industry asked Armstrong to replace four constant-speed pumps with three Design Envelope pumps, and changed their system to use primary-variable control.


HVAC savings as a result of the retrofit project were over \$7,900, which represented a 43% decrease in spending year-over-year. The payback period for the investment in energy efficiency was just 1¹/₂ years.



ven the best equipment and installations require attention from time to time. Genuine factory parts keep your Armstrong equipment and systems operating reliably with a long service life — the way they were originally designed for. Call our Field Assistance at +1 416 755 2298 or your local authorized Armstrong Service Dealer.

FEATURE REPLACEMENT PART: DROP-IN UPGRADE

The Design Envelope Vertical In-Line Retrofit Solution lets you upgrade a constant speed pump to an intelligent, Sensorless, variable speed solution



pump models

4300/4380 Vertical In-Line pumps | 132 pump models in 14 casing sizes 4312/4392 Vertical In-Line Twin pumps | 39 pump models in 7 casing sizes 4302/4382 Vertical In-Line dualArm pumps | 59 pump models in 9 casing sizes All VIL Retrofit units are performance tested using a matching casing.

ARMSTRONG PARTS KITS: ENGINEERED AND PRE-ASSEMBLED

rmstrong Parts Kits are engineered combinations of genuine replacement parts — planned, selected and packaged based on solution types and sizes. Use Parts Kits for maintenance projects to add value to your building operators and service personnel.



REPLACEMENT PARTS



CASE STUDY



Commercial Towers

26

he owners of this pair of commercial towers recently completed an hvac upgrade, replacing three constant speed pumps with new Design Envelope pumps with Pump Manager.

Along with the energy savings, Pump Manager provided system warnings that helped avoid expensive repairs and energy losses.



27 ACCESSORIES

o make sure you get the best possible results from your mechanical room designs and installations we carry an assortment of high-quality ancillary products. By using Armstrong accessories you can be certain no quality low points and operating bottlenecks get in the way of your system performance.

 Multi-function pump fittings that provide a 90° elbow, guide vanes, and an in-line strainer.
 Suction guides reduce pump installation cost and floor space requirements

NVELOP

DESIGN

- Suitable for all Armstrong commercial pumps and pumping systems
- Size: 1½" to 20"

SUCTION GUIDES

 Multi-function pump fittings that reduce equipment and installation costs
 Suitable for all Armstrong commercial pumps

• Size: 1½" to 20"

FLO-TREX VALVES

• Designed to reduce tank sizes by up to 80% over standard designs

 Range: AET plain steel expansion tanks: 15 to 525 US gal. capacity; AX diaphragm expansion tanks: 8 to 211 US gal. capacity; Type L bladder type expansion tanks: 10 to 1056 US gal. capacity



• Designed to eliminate trapped air and suspended dirt particles associated with the start-up and maintenance of hydronic and HVAC systems



DIRT & AIR SEPARATORS

- Provide automatic glycol make-up for HVAC systems. The specially molded mixing tank offers a compact package with built-in housing for controls and make-up pump
- Suitable for all bladder and compression tanks up to 90 psi (621 kPa) cold-fill pressure

GLYCOL AUTOFILL UNITS



 ½" to 2" models feature multi-turn adjustment for precise control, hidden memory stops to set balance point and soft seats for positive shutoff
 Temperature: -4°F to 300°F

• Size: ½" to 2"

CIRCUIT BALANCING VALVES (½"-2")



 2½" to 12" models feature multi-turn adjustment for precise control, hidden memory stops to set balance point and soft seats for positive shutoff

Temperature: 230°F
Size: 2¹/₂" to 12"

CIRCUIT BALANCING VALVES (2"-12")







ACCESSORIES

- Built with high-quality materials for premium energy-efficiency and long service life
- Designed for class B temperature rise and equipped with superior class F insulation. Maximum ambient temp 40°C (unless approved differently)
- Power: 0.33 hp to 1250 hp

MOTORS



CASE STUDY



Delta Hotel


elta Hotels Toronto commissioned an upgrade of one of their existing pumps to a new Design Envelope Tango. Energy savings postinstallation have proven that the Tango pump was the right choice.

Savings from upgrading just one pump will be over \$2,000 per year. Total energy savings will be 22,000 kWh, a 40% improvement.





our core expertise of fluid flow, energy transfer, demand-based control and digitalization mitigates risk and reduces complexity.




BRINGING IT ALL TOGETHER

30

WHY USE VERTICAL IN-LINE (VIL) PUMPS VS. HORIZONTAL DESIGN?

WHY USE DESIGN ENVELOPE INTEGRATED CONTROLS VS. WALL-MOUNTED DRIVES?



DESIGN ENVELOPE INTEGRATED CONTROLS

Minimal project and operating risk through three-year warranty on controls and pump

Single point of supplier accountability

Factory tested and configured

Superior energy efficiency and envelope control compared to "non-native" controls (such as wall-mounted drives)

Integrated 5% line isolation (no need for separate transformer)

Elimination of grounding rings (optional in case of concern)

Outdoor option up to 125 HP (no enclosure required)

Elimination of wiring (power and control) between pump and wall-mounted drive

Elimination of differential-pressure sensor as well as associated wiring and labor (in case of concern Design Envelope can read sensor input)

What makes Armstrong different?

No other company integrates demandbased controls, heat transfer, fluid flow and variable speed as well as Armstrong, adding value to your project.

Only Armstrong has patented, awardwinning, proprietary Parallel Sensorless pumping technology, delivering unmatched efficiency with multiple pumps.

Armstrong's integrated capability offers unmatched scalability and flexibility, opening up significant application opportunities. Only Armstrong offers intelligent, self-aware and self-optimizing solutions that combine to deliver optimum building performance.

Only Armstrong can deliver both the lowest installed cost AND the lowest operating cost time after time.

Only Armstrong factory tests and programs each unit, resulting in the accuracy and repeatability of all our solutions from custom large plants to small components.

Armstrong is privately held, allowing us to take a long-term perspective on the success of your project.

WHERE TO BUY

Armstrong products, services, and replacement parts are available nationwide from our authorized representatives, distributors, wholesalers, and service dealers.

Visit ArmstrongFluidTechnology.com to find your local representative



ARMSTRONG FLUID TECHNOLOGY ESTABLISHED 1934

ARMSTRONG FLUID TECHNOLOGY®